


2-Wire eurofast® Cordsets, Standard Plug Body

- Straight Female Connector
- NEMA 1, 3, 4, 6P and IEC IP 68 Protection
- 250 VAC/300 VDC, 4 A



Housing Style	Part Number	Cable	Features	Pinout
	RK 4.2T-*	AWM PVC Grey 2x20 AWG 105°C 5.2 mm OD Cable #RF50529-*M†	flexlife®	1. N/C 2. N/C 3. BN 4. BU
	RK 4.2T-*/S90	AWM PUR Grey 2x20 AWG 105°C 5.2 mm OD Cable #RF50772-*M†	Cut/Abrasion Immune	
	RK 4.2T-*/S748	AWM PVC Yellow 2x22 AWG 105°C 5.2 mm OD Cable #RF50650-*M†		1. WH 2. N/C 3. N/C 4. BK
	RK 4.21T-*/S1511	AWM PVC Grey 2x20 AWM PVC 105°C 5.2 mm OD Cable #RF50529-*M†	flexlife	
	RK 4.21T-*	AWM PVC NAMUR Blue 2x20 AWG 105°C 5.2 mm OD Cable #RF20003-*M†		1. BN 2. BU 3. N/C 4. N/C
	RK 4.21T-*/S90	AWM PUR NAMUR Blue 2x20 AWG 105°C 5.2 mm OD Cable #RF50657-*M†	Cut/Abrasion Immune	
	RK 4.22T-*	AWM PVC Grey 2x20 AWG 105°C 5.2 mm OD Cable #RF50529-*M†	flexlife	1. BN 2. N/C 3. BU 4. N/C
	RK 4.23T-*	AWM PVC Grey 2x20 AWG 105°C 5.2 mm OD Cable #RF50529-*M†		1. BN 2. N/C 3. N/C 4. BU



* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.

** Standard coupling nut material is nickel plated brass "RK .."; "RKK .." indicates nylon and "RKV .." indicates 316 stainless steel.

† See Section N for reelfast® cable information.