

4		3		2		1																																					
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION																																							
© COPYRIGHT - By -				ALL RIGHTS RESERVED.																																							
LOC G		DIST 14		REVISIONS																																							
P		LTR		DESCRIPTION		DATE	DWN	APVD																																			
		M3		REVISED PER ECO-11-004820		11MAR11	RK	HMR																																			
AMP WIRE RANGE		UL Listed FILE E13288		LR7189 Certified																																							
16-14 AWG SOLID OR STRANDED		16-14 AWG SOLID OR STRANDED		16-14 AWG SOLID OR STRANDED																																							
SERRATIONS WIRE STOP INSULATION BODY AMP AMP AMP A 27.05 MAX [1.065] STYLE 1				SERRATIONS WIRE STOP INSULATION BODY AMP AMP AMP AM 28.07 MAX [1.105] STYLE 2				1. WIRE INSUL DIA, 2.92-4.32 [.115-.170] 2 TAPE, NO STICKY																																			
				1 2 <table><tr><td>I</td><td>50</td><td>LOOSE PIECE, BAG</td><td>8-34071-5</td></tr><tr><td>I</td><td>5</td><td>LOOSE PIECE, BLS</td><td>8-34071-4</td></tr><tr><td>I</td><td>100</td><td>LOOSE PIECE, BOX</td><td>8-34071-1</td></tr><tr><td>2</td><td>2500</td><td>ON TAPE, REEL</td><td>4-34071-4</td></tr><tr><td>2</td><td>2500</td><td>ON TAPE, REEL</td><td>2-34071-3</td></tr><tr><td>2</td><td>1000</td><td>LOOSE PIECE</td><td>2-34071-2</td></tr><tr><td>I</td><td>2500</td><td>ON TAPE, REEL</td><td>2-34071-1</td></tr><tr><td>I</td><td>1000</td><td>LOOSE PIECE</td><td>34071</td></tr><tr><td>STYLE</td><td>QTY</td><td>PACKAGE TYPE</td><td>PART NO</td></tr></table>				I	50	LOOSE PIECE, BAG	8-34071-5	I	5	LOOSE PIECE, BLS	8-34071-4	I	100	LOOSE PIECE, BOX	8-34071-1	2	2500	ON TAPE, REEL	4-34071-4	2	2500	ON TAPE, REEL	2-34071-3	2	1000	LOOSE PIECE	2-34071-2	I	2500	ON TAPE, REEL	2-34071-1	I	1000	LOOSE PIECE	34071	STYLE	QTY	PACKAGE TYPE	PART NO
I	50	LOOSE PIECE, BAG	8-34071-5																																								
I	5	LOOSE PIECE, BLS	8-34071-4																																								
I	100	LOOSE PIECE, BOX	8-34071-1																																								
2	2500	ON TAPE, REEL	4-34071-4																																								
2	2500	ON TAPE, REEL	2-34071-3																																								
2	1000	LOOSE PIECE	2-34071-2																																								
I	2500	ON TAPE, REEL	2-34071-1																																								
I	1000	LOOSE PIECE	34071																																								
STYLE	QTY	PACKAGE TYPE	PART NO																																								
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 90°C [194° F]		THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN M ELLIS 19JUL95		TE Connectivity																																	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK C PRESNELL 19JUL95																																	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] SOLID OR STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD S BORTNER 19JUL95																																	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL BODY, CU ASTM B 152 SLV, PVC, COLOR-BLUE		FINISH TIN PLATE ASTM B545		NAME SPLICE, BUTT, PLASTI-GRIP WIRE SIZE 16-14 AWG																																	
										PRODUCT SPEC UL486A																																	
										APPLICATION SPEC																																	
										SIZE A3																																	
										CAGE CODE 00779																																	
										DRAWING NO C-34071																																	
										RESTRICTED TO																																	
										SCALE 4:1																																	
										SHEET 1 OF 1																																	
										REV M3																																	
										CUSTOMER DRAWING																																	