


LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
			G1	REVISED PER ECO-14-019230	03APR2015	DR

 WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
24-20 AWG SOLID OR STRANDED	22-20 AWG SOLID OR STRANDED	22-20 AWG SOLID OR STRANDED



- 1


STAMP AMP APPROX AS SHOWN.
- 2

MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS.
- 3

COPPER PER ASTM B-152, ANNEALED
- 4


TIN PLATE 0.00254 [$.000100$] MIN PER ASTM B-545
- 5

NOTE DELETED.



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C[338°F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.16-0.65mm² [320-1,290] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	

100	LOOSE PIECE, BOX	4	8-324001-1
1000	LOOSE PIECE	4	324001
QTY	PACKAGE TYPE	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-13-93	 TE Connectivity			
DIMENSIONS: MM[INCHES]		CHK DA PATTERSON 4-13-93				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SPLICE, BUTT, STRAP, SOLISTRAND			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -					
	FINISH					
MATERIAL COPPER 	SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C-324001	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 10:1		SHEET 1 of 1	REV G1