



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
DF	SO		G	REV & REDRAWN,0600-6242-97	4-97	CT
						SG



- ¹ TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
- ² AMP INFORMATION MARKED PER MIL-STD-130.
- ³ CUSTOMER MARKING MARKED PER MIL-STD-130 OPPSITE AMP INFO ON -1 ONLY.
4. TO MATE WITH AMP LGH-1/2
RECEPTACLE WITH .53 [13.5] BARREL DEPTH.

OBSOLETE	-	24.00 [609.6]	863330-2
	3A2P2	18.00 [457.2]	863330-1
	CUSTOMER MARKING	DIM A ¹	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 4-21-97	AMP AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: INCHES [mm]		CHK S.GLATFELTER 5-5-97			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±.02 [0.5] 3 PLC ±.005 [0.13] 4 PLC ±- ANGLES ±- FINISH -	APVD S.GLATFELTER 5-5-97	NAME LEAD ASSY,DBL END,RFI SHIELDED,LGH-1/2		
		PRODUCT SPEC -	SIZE A2		
		APPLICATION SPEC -	CAGE CODE 00779		
		MATERIAL -	WEIGHT -	DRAWING NO C-863330	
CUSTOMER DRAWING		SCALE 2:1		SHEET 1 OF 1	REV G