





|                                                      |               |
|------------------------------------------------------|---------------|
| ITEM-NO. (ITEM-NO.)                                  | 727-224       |
| Cross section1 (Cross section / mm <sup>2</sup> )    | 0.08 - 1.5    |
| Cross section2 (Cross section / AWG)                 | 28 - 16       |
| Strip length (Strip length / mm)                     | 8 - 10        |
| Measured voltage (Measured voltage / V)              | 250           |
| Measured shock voltage (Measured shock voltage / kV) | 4             |
| Pollution degree (Pollution degree)                  | 3             |
| Current intensity (Current intensity / A)            | 12            |
| Height (Height / mm)                                 | 44.5          |
| Width (Width / mm)                                   | 7.62          |
| Depth (Depth / mm)                                   | 126           |
| No. of connection Points (No. of connection Points)  | 16            |
| No. of potentials (No. of potentials)                | 4             |
| COLOR (COLOR)                                        | blau          |
| WEIGHT (WEIGHT / g)                                  | 32.12         |
| Comment (Comment)                                    | ohne Aufdruck |