

6		5		4		3		2		19205	
MATERIAL NO.		ENG. NO.		WIRE SIZE		I.D. MIN.		O.D. MAX.		"L" (E)	
192070001		AS-302		22-18		.060/1.50		.130/3.30		.305/.325 (7.75/8.26)	
192050001		BS-304		16-14		.091/2.30		.160/4.10		.295/.315 (7.50/8.00)	
192050003		CS-303		12-10		.130/3.30		.225/5.70		.295/.315 (7.50/8.00)	
192050004		D-355		8		.165/4.20		.295/7.50		.360/.390 (9.14/9.91)	
192050006		E-361		6		.230/5.80		.374/9.50		.430/.460 (10.92/11.68)	
192050007		F-365		4		.277/7.00		.457/11.60		.500/.530 (12.70/13.46)	
192050008		G-373		2		.357/9.00		.538/13.70		.635/.665 (16.13/16.89)	
192050009		H-384		1/0		.439/11.20		.620/15.70		.735/.765 (18.67/19.43)	
192050010		J-389		2/0		.496/12.60		.697/17.70		.725/.755 (18.42/19.18)	
192150049		K-394		3/0		.545/13.80		.760/19.30		.735/.765 (18.67/19.43)	
192150050		L-379		4/0		.621/15.80		.860/21.80		.760/.790 (19.30/20.07)	