


HONEYWELL
PART NUMBER

BZ-7RW825520-A2-S

REV	DOCUMENT	CHANGED BY	CHECK
A	0041984	SS 24JUL08	BLR



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF
.139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

CATALOG LISTING AQL9302
REPLACES X201403-BZ

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH		DRAWN	SS	24JUL08	Honeywell						
		CONTACT ARRANGEMENT		TOLERANCES UNLESS NOTED:		CHECK	BD	24JUL08							
OPERATING FORCE----- 5 OZ MAX		L96 15A 125, 250 OR 480 VAC 1/8 HP 125 VAC, 1/4 HP 250 VAC 1/2A 125 VDC, 1/4A 250 VDC L288 CE SF 16A 250V T85 5E4 L315 L306		NO PLACES X ± -		THIS DRAWING COVERS A PROPRIETARY ITEM			TITLE						
RELEASE FORCE----- 3/4 OZ MIN				ONE PLACE .X ± .03		AND IS THE PROPERTY OF HONEYWELL.									
DIFFERENTIAL TRAVEL----- .040 - .062				TWO PLACE .XX ± .015		THIS DRAWING IS NOT TO BE COPIED OR USED									
OVERTRAVEL----- .156 MIN				THREE PLACE .XXX ± .005		WITHOUT THE PERMISSION OF HONEYWELL.									
				ANGLES X ± -		INTERPRET PER ANSI Y14.5M-1982			SIZE	TYPE	CAGE CODE	DRAWING NAME		REV	
				THIRD ANGLE PROJECTION		OTHER HONEYWELL ENGINEERING			B	I	-	BZ-7RW825520-A2-S		A	
						STANDARDS MAY APPLY			RASTER	SCALE	-	WEIGHT	.076 LB	SHEET	1 OF 1