

APPLIES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS AND MAY BE USED ONLY FOR THE PURPOSES FOR WHICH IT WAS PROVIDED. IT MAY NOT BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

THIS DRAWING IS A CONTROLLED DOCUMENT.
REV NO

LOC
CE
DIST
16

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ (No Pins), Black			ST	
			IL (dB)	RL (dB)		IL (dB)	RL (dB)
0-6278298-1	0.950 - 1.050	3.11 - 3.44	0.5	26		0.5	50
0-6278298-2	1.950 - 2.050	6.39 - 6.72	0.5	26		0.5	50
0-6278298-3	2.950 - 3.050	9.67 - 10.00	0.5	26		0.5	50
0-6278298-4	3.920 - 4.080	12.86 - 13.38	0.5	26		0.5	50
0-6278298-5	4.920 - 5.080	16.14 - 16.66	0.5	26		0.5	50
0-6278298-6	5.920 - 6.080	19.42 - 19.94	0.5	26		0.5	50
0-6278298-7	6.920 - 7.080	22.70 - 23.22	0.5	26		0.5	50
0-6278298-8	7.920 - 8.080	25.98 - 26.50	0.51	26		0.51	50
0-6278298-9	8.850 - 9.150	29.03 - 30.01	0.51	26		0.51	50
1-6278298-0	9.850 - 10.150	32.31 - 33.30	0.51	26		0.51	50
1-6278298-1	10.850 - 11.150	35.59 - 36.58	0.51	26		0.51	50
1-6278298-2	11.850 - 12.150	38.87 - 39.86	0.51	26		0.51	50
1-6278298-3	12.850 - 13.150	42.15 - 43.14	0.51	26		0.51	50
1-6278298-4	13.850 - 14.150	45.43 - 46.42	0.51	26		0.51	50
1-6278298-5	14.850 - 15.150	48.72 - 49.70	0.51	26		0.51	50
1-6278298-6	15.840 - 16.160	51.96 - 53.01	0.51	26		0.51	50
1-6278298-7	16.830 - 17.170	55.21 - 56.33	0.51	26		0.51	50
1-6278298-8	17.820 - 18.180	58.46 - 59.64	0.51	26		0.51	50
1-6278298-9	18.810 - 19.190	61.71 - 62.95	0.51	26		0.51	50
2-6278298-0	19.800 - 20.200	64.96 - 66.27	0.51	26		0.51	50
2-6278298-1	20.790 - 21.210	68.20 - 69.58	0.51	26		0.51	50
2-6278298-2	21.780 - 22.220	71.45 - 72.90	0.52	26		0.52	50
2-6278298-3	22.770 - 23.230	74.70 - 76.21	0.52	26		0.52	50
2-6278298-4	23.760 - 24.240	77.95 - 79.52	0.52	26		0.52	50
2-6278298-5	24.750 - 25.250	81.20 - 82.84	0.52	26		0.52	50
2-6278298-6	25.740 - 26.260	84.44 - 86.15	0.52	26		0.52	50
2-6278298-7	26.730 - 27.270	87.69 - 89.46	0.52	26		0.52	50
2-6278298-8	27.720 - 28.280	90.94 - 92.78	0.52	26		0.52	50
2-6278298-9	28.710 - 29.290	94.19 - 96.09	0.52	26		0.52	50
3-6278298-0	29.700 - 30.300	97.44 - 99.40	0.52	26		0.52	50
3-6278298-1	30.690 - 31.310	100.68 - 102.72	0.52	26		0.52	50
3-6278298-2	31.680 - 32.320	103.93 - 106.03	0.52	26		0.52	50
3-6278298-3	32.670 - 33.330	107.18 - 109.35	0.52	26		0.52	50
3-6278298-4	33.660 - 34.340	110.43 - 112.66	0.52	26		0.52	50
3-6278298-5	34.650 - 35.350	113.68 - 115.97	0.52	26		0.52	50
3-6278298-6	35.640 - 36.360	116.92 - 119.29	0.53	26		0.53	50
3-6278298-7	36.630 - 37.370	120.17 - 122.60	0.53	26		0.53	50
3-6278298-8	37.620 - 38.380	123.42 - 125.91	0.53	26		0.53	50
3-6278298-9	38.610 - 39.390	126.67 - 129.23	0.53	26		0.53	50
4-6278298-0	39.600 - 40.400	129.92 - 132.54	0.53	26		0.53	50
5-6278298-0	49.500 - 50.500	162.40 - 165.68	0.54	26		0.54	50

Qty	U of M	Description	Item No.
1	piece	HOUSING, CONN, MT-RJ,BLACK	1
1	piece	DUST COVER, MT-RJ	2
1	piece	SPRING, MT-RJ, 3.8 DESIGN	3
1	piece	PIN KEEPER, 3.8MM	4
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	5
1	piece	CRIMP EYELET, MT-RJ	6
0.0139	sheet	Leg Label - "A"	7
0.0139	sheet	Leg Label - "B"	8
1	piece	MT-RJ FERRULE, THERMOPLAST SM	9
2	piece	Crimp Eyelet	10
2	piece	ST Short Boot - 1.6 to 2.0mm, Blue	11
2	piece	PVC Build-up tubing	12
2	piece	CONN ASSY,2.5MM BAY,SM, 126 UM	13
AR	meter	2 fiber, SM, 1.8 mm, Twinzip, Yellow, OFNR (Riser)	14
1	piece	MT-RJ TwinZip Bend Limiting Boot, Blue	15
2	piece	Trace Label	16

	B	Rev Per EC#	06-022379	9/27/2006	-	MK	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS: meters		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 P.L.C ±	±
		1 P.L.C ±	±
		2 P.L.C ±	±
		3 P.L.C ±	±
		4 P.L.C ±	±

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK Michael Kepko				
APVD Michael Kepko				
NAME FO C/A - 2 fiber, SM, OFNR (Riser) jacket, MT-RJ (No Pins) to ST				
SCALE NTS	SIZE A2	DRAWING NO C- 6278298		SHEET 2 of 3
				REV B

8 7 6 5 4 3 2 1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

XXXXXXXXXXXXXXXXXX

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

B	Rev Per EC#	06-022379	9/27/2006	-	MK	
P	LTR	REVISION RECORD	DATE	DIN	APVD	

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
meters	
	0 P.L.C. ± .
	1 P.L.C. ± .
	2 P.L.C. ± .
	3 P.L.C. ± .
	4 P.L.C. ± .

Customer Print

DIN Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Michael Kepko	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD	Michael Kepko			
NAME FO C/A - 2 fiber, SM, OFNR (Riser) jacket, MT-RJ (No Pins) to ST				
SCALE	SIZE	DRAWING NO	SHEET	REV
NTS	A2	C- 6278298	3 of 3	B

8

7

6

5

4

3

2

1