


Holding and Fastening Products

Communications Duct

Communications Duct is the ideal solution when cable or wires cannot be installed within the wall. Duct is available in six sizes. A co-extruded hinge allows access to wire and cable without stress cracking or discoloration. Five colors—NEMA ivory, brown, ash, gray and white—blend discreetly with today’s office environment and custom colors are available for volume purchase.

- Other features include:
- Positive latching for easier, more secure installation of wires
 - Ultra-strong foam-backed adhesive mounts quickly, even on masonry walls
 - Modern symmetrical design means fewer components; hides latch from sight
 - One-piece design for easier installation
 - Constructed of UL-listed PVC
 - Wider base for greater adhesive strength and longer product life; base conforms to accessories for a more uniform appearance
- For sizes, color options, and ordering information, see chart on page 203.



325

Communication Duct Accessories

Communications Duct Accessories are available in corresponding sizes and colors for each of the three duct sizes. Accessories include joint covers, outside corners, inside corners, tees, end caps, elbows and reducers.




326

Surface Mount Kits

Two sizes of junction boxes—High Profile and Low Profile—facilitate various outlet installations and provide easy access to wires and splice points. Available in all five standard colors.

Size: High Profile- 50 mm (2.0") H x 122.6 mm (4.83") W x 92 mm (3.625") D

Size: Low Profile- 25.3 mm (1.0") H x 122.6 mm (4.83") W x 92 mm (3.625") D



327

Ordering Information for Communications Duct



Description	Ivory	UPC	Ash	UPC	Gray	UPC	White	UPC	Min. Order
1.9 cm x 1.3 cm x 1.2 m (0.5"H x 0.75"W x 4'L)	801I	054007-68550	801A	054007-68552	801G	054007-68549	801W	054007-91786	10/cs.
3.2 cm x 1.9 cm x 1.2 m (0.75"H x 1.25"W x 4'L)	802I	054007-68554 [402266]	802A	054007-68556	802G	054007-68553	802W	054007-91787	10/cs.
4.4 cm x 2.5 cm x 1.2 m (1.0"H x 1.75"W x 4'L)	803I	054007-68558	803A	054007-68560	803G	054007-68557	803W	054007-91788	10/cs.
1.9 cm x 1.3 cm x 1.8 m (0.5"H x 0.75"W x 6'L)	801I-6'	051138-57267	801A-6'	051138-11529	801G-6'	051138-11548	801W-6'	054007-91786	10/cs.
3.2 cm x 1.9 cm x 1.8 m (0.75"H x 1.25"W x 6'L)	802I-6'	051138-57268	802A-6'	051138-11530	802G-6'	051138-11549	802W-6'	054007-91675	10/cs.
4.4 cm x 2.5 cm x 1.8 m (1.0"H x 1.75"W x 6'L)	803I-6'	051138-57269	803A-6'	054007-92702	803G-6'	051138-11550	803W-6'	054007-91674	10/cs.
1.9 cm x 1.3 cm x 2.4 m (0.5"H x 1.75"W x 8'L)	—	—	—	—	—	—	801W-8'	054007-91637	200
4.4 cm x 1.3 cm x 2.4 m (1.0"H x 0.75"W x 8'L)	801I-8'	054007-91670	—	—	—	—	—	—	200
1.3 cm x 1.9 cm x 2.4 m (0.75"H x 1.25"W x 8'L)	802I-8'	056007-91669	—	—	—	—	802W-8'	054007-91672	200
4.4 cm x 2.5 cm x 2.4 m (1.0"H x 1.75"W x 8'L)	803I-8'	056007-91668	—	—	—	—	803W-8'	054007-91671	2000

Accessories

Joint Cover	801I-JC	054007-68570	801A-JC	054007-68572	801G-JC	054007-68569	801W-JC	054007-91768	50/cs.
Joint Cover	802I-JC	054007-68596	802A-JC	054007-68598	802G-JC	054007-68595	802W-JC	054007-91769	50/cs.
Joint Cover	803I-JC	054007-71175	803A-JC	054007-71177	803G-JC	054007-71174	803W-JC	054007-91770	50/cs.
Outside Corner	801I-OC	054007-68582	801A-OC	054007-68584	801G-OC	054007-68581	801W-OC	054007-91765	50/cs.
Outside Corner	802I-OC	054007-71163	802A-OC	054007-71165	802G-OC	054007-71161	802W-OC	054007-91766	50/cs.
Outside Corner	803I-OC	054007-71188	803A-OC	054007-71190	803G-OC	054007-71187	803W-OC	054007-91767	50/cs.
Inside Corner	801I-IC	054007-68578	801A-IC	054007-68580	801G-IC	054007-68577	801W-IC	054007-91771	50/cs.
Inside Corner	802I-IC	054007-71158	802A-IC	054007-71160	802G-IC	054007-68603	802W-IC	054007-91772	50/cs.
Inside Corner	803I-IC	054007-71184	803A-IC	054007-71186	803G-IC	054007-71183	803W-IC	054007-91773	50/cs.
Tee	801I-T	054007-68562	801A-T	054007-68564	801G-T	054007-68561	801W-T	054007-91774	50/cs.
Tee	802I-T	054007-68588	802A-T	054007-68590	802G-T	054007-68587	802W-T	054007-91775	50/cs.
Tee	803I-T	054007-71167	803A-T	054007-71169	803G-T	054007-71166	803W-T	054007-91776	50/cs.
End Cap	801I-EC	054007-68574	801A-EC	054007-68576	801G-EC	054007-68573	801W-EC	054007-91777	50/cs.
End Cap	802I-EC	054007-68600	802A-EC	054007-68602	802G-EC	054007-68599	802W-EC	054007-91778	50/cs.
End Cap	803I-EC	054007-71180	803A-EC	054007-71182	803G-EC	054007-71179	803W-EC	054007-91779	50/cs.
Elbow	801I-L	054007-68566	801A-L	054007-68568	801G-L	054007-68565	801W-L	054007-91780	50/cs.
Elbow	802I-L	054007-68592	802A-L	054007-68594	802G-L	054007-68591	802W-L	054007-91781	50/cs.
Elbow	803I-L	054007-71171	803 A-L	054007-71173	803G-L	054007-71170	803W-L	054007-91782	50/cs.
Reducer-803 to 802	803I-R2	054007-71192	803A-R2	054007-71194	803G-R2	054007-71191	803W-R2	054007-91783	25/cs.
Reducer-803 to 801	803I-R1	054007-71196	803A-R1	054007-71198	803G-R1	054007-71195	803W-R1	054007-91784	25/cs.
Reducer-802 to 801	802I-R1	054007-71200	802A-R1	054007-71202	802G-R1	054007-71199	802W-R1	054007-91785	25/cs.


Surface Mount Kits (kit includes adhesive-backed base, cover, and screws)

High-Profile Box	800I-HB	054007-71204	800A-HB	054007-71206	800G-HB	054007-71203	800W-HB	054007-91763	10/cs.
Low-Profile Box	800I-LB	054007-71208	800A-LB	054007-71210	800G-LB	054007-71207	800W-LB	054007-91764	10/cs.

790 Cable Tie and Base Assembly



For securing cable and cable bundles to a surface, the self-locking cable tie can be removed and replaced with another 760 Cable Tie when desired. For cable or bundles with maximum O.D. of 45 mm (1-3/4"). Adhesive-backed base has knock-out holes for screws. Base color: Ivory. Ties: Clear. Size: Base, 25 mm x 50 mm (1" x 2"). Tie length: 182 mm (7.18").



328

792 Cable Tie and Base Assembly



For securing cable bundles of 125 mm (1") or less. Base color: Ivory. Ties: Clear. Size: 25 mm x 25 mm (1" x 1") Tie length: 182 mm (7.18").




329

Cable Clips



Clips are made of vinyl with foam adhesive backing. They may be mounted on most clean, dry surfaces without drilling.

- Fit cables from 3.18 mm (1/8") to 12.7 mm (1/2")
- Low profile
- Eliminate drilling and nailing
- Use for internal equipment wiring and around desks, furniture and machines
- Wire can be removed without removing clip
- Clips made of flame retardant material (Oxygen index > 28)



330

Cable Ties



Self-locking, clear plastic ties are used to bundle and secure conductors or cable.

Cable Ties and Bases



Cable Ties and Tie-Base Assemblies are available in various sizes for securing cable and cable bundles to a surface. Bases are adhesive-backed, with screw mounting provisions.

- All-nylon ties
- ABS base
- Flame retardant
- Fungus insert
- Solvent resistant
- Service temperature range -40° to 85°C (-40° to 185°F)



331

Ordering Information for Holding and Fastening Products

Product Number	Packaging kg (lbs.)/cs.	Minimum Order	UPC
Cable Clips-Size: mm (in.)/Max Cable O.D. 706 Size: 25 (1), Max. Cable O.D.: 3 (1/8) 707 Size: 25 (1), Max. Cable O.D.: 6 (1/4) 708 Size: 32 (1-1/4), Max. Cable O.D.: 5 (3/16) 710 Size: 38 (1-1/2), Max. Cable O.D.: 6 (1/4) 712 Size: 44 (1-3/4), Max. Cable O.D.: 8 (5/16) 713 Size: 51 (2), Max. Cable O.D.: 10 (3/8)	100/bag, 1000/cs., 1.5 (3.2) 100/bag, 1000/cs., 3.0 (6.7) 100/bag, 1000/cs., 2 (4.5) 100/bag, 1000/cs., 2.4 (5.2) 100/bag, 1000/cs., 3.86 (8.5) 100/bag, 1000/cs., 5.35 (11.8)	1000 each 1000 each 1000 each [550977] 1000 each 1000 each [550979] 1000 each [550980]	054007-12972 054007-30445 054007-12998 054007-13012 054007-21387 054007-21429
Cable Ties 06264-Heavy Duty 380 mm (15") Double Loop Cable Ties 06266-Standard 387 mm (15-1/4") 06267-Heavy Duty 397 mm (15-5/8") Mounting Cable Ties 06256-Standard 392 mm (15-7/16") 06258-Standard 392 mm (15-7/16") 06269-Heavy Duty 397 mm (15-5/8")	500/bag, 2500/cs., 11.3 (25.0) 500/bag, 2500/cs., 5.9 (13.0) 500/bag, 2500/cs., 15 (33) 1000/bag, 10,000/cs., 12.7 (28.0) 500/bag, 2500/cs., 7.3 (16.0) 500/bag, 2500/cs., 14.5 (32.0)	2500 each 2500 each 2500 each 10,000 each 2500 each 2500 each	054007-06264 054007-06266 054007-06267 054007-06256 054007-06258 054007-06269
790 Cable Tie and Base Assembly	100/bag, 1000/cs., 7.8 (17.2)	1000 each [557607]	054007-11115
792 Cable Tie and Base Assembly	100/bag, 1000/cs., 1.4 (3.1)	1000 each [557609]	054007-27618