



Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

 **Text Search: 'NKSOPBUY'**

Your search criteria matched only one product, shown below

NKSOPBUY

- TIA/EIA-604 FOCIS-6 compliant connectors
- Exceed TIA/EIA-568-B.3 requirements
- Insertion loss: .1dB typical (multimode), .2dB typical (singlemode)
- Return loss: >20dB (multimode), >40dB (singlemode)
- RJ45 small form factor duplex plug
- Non-optical disconnect maintains data transmission under tensile loads
- Each duplex plug includes housing, insert, two ferrule assemblies, two crimp sleeves, one boot for 3mm jacketed cable and two dust caps
- Fiber cable type: tight-buffered recommended
- Fiber cable size: 3.0mm jacketed cable or 1.6mm - 2.0mm jacketed cable (noted in part description)
- Ferrule type: 2.5mm zirconia ceramic (highest durability for repeated matings)
- Field polish termination -- *PANDUIT*® recommends anaerobic adhesive
- Use Field Polish Termination Kit (FJKITG)

▪ Part Number	NKSOPBUY
▪ RoHS Compliancy Status	Compliant
▪ Part Description	NetKey® FJ® singlemode duplex plug.
▪ Product Type	Fiber Optic Adapter Modules
▪ Color	Blue
▪ CE Compliant	No
▪ Pricing Description	NetKey Opti-Plug Singlemode Fiber Connector
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.