

About Leviton

A Century of Success

Press

Join Our eMailing List

Trade Shows

RoHS

Career Opportunities

Contact Us

All Leviton Products

Electrical

Network Solutions

Lighting Controls

Entertainment

Home Automation

Connected Home

Energy Management

Power Quality

Library Home

Application Notes

Brochures / Catalogs

Case Studies

DDLs

Downloads

Drawings

Line Cards

Manuals / Instructions

Product Specifications / Datasheets

Software

Specs (AIA / CSI)

Take One

Tech Notes

Technical Articles

Videos

ez-Biz

ez-Find

ez-Learn

ez-Configurator

Distribution Home

Contractor Connection

ez-Learn

ez-Find

Sign In - B2B

OEM Home

How to Buy

Whats New

Press/News

Retail Home

Product Information

How To

Merchandising

Energy Smart Living

International Home

China (English)

China (Chinese)

Mexico (English)

Mexico (Spanish)

Middle East (English)

International Contact

Press

Products

Trade Shows

Made to Order

EZE-Rough

Acenti Devices

AC Switches

Appliance Switches

Architectural Controls

Camera Systems

Combination Devices

Connectors & Cables

Cord Sets

Corrosion Resistant Devices

Daylighting Controls

Decora Devices

Dimmers

Cam-Type Devices


Electrical Accessories

Entertainment Accessories

Entertainment Fixtures

Entertainment Lighting Controls

Entertainment Lighting Kits



- ≥

Electrical
- ≥

Network Solutions
- ≥

Lighting Controls
- ≥

Entertainment
- ≥

Home Automation
- ≥

Connected Home
- ≥

Energy Management
- ≥

Power Quality


ZOOM

Quantity:

1


Color:

Yellow



NEMA:

5-15P



5256-VA

Description

15 Amp, 125 Volt, NEMA 5-15P, 2P, 3W, Plug, Straight Blade, Industrial Grade, Grounding, Python Angle - Yellow

Additional Product Information

- [Dimensional Drawing](#)
- [Wiring Diagram](#)

Product Features

Grounding: Grounding
Feature: Python
Amperage: 15 Amp
Voltage: 125 Volt
NEMA: 5-15P
Pole: 2
Wire: 3
Cord Range: .250 - .650
Wire Gauge: 18-10 AWG
Blades/Contacts: Solid Brass
Body Material: Nylon
Assembly Screws: Steel, Zinc Plated
Color: Yellow
Standards and Certifications: UL/CSA
Warranty: 2 Year Limited

Features and Benefits

- Tough high-impact body
- Hinged design delivers fast, easy installation and assembly
- Triple-drive screws for easy wiring - Standard, Phillips, Robertson
- Wide Cord Clamp Range, 18-3 SVT-10-3 ST, (.250"-.650")
- Backed by a 2-Year Warranty

Electrical Specifications	
Temperature Rise:	Max 30C after 250 cycles OL at 200 percent rated current
Dielectric Voltage:	Withstands 2000V per UL498
Current Interrupting:	Certified for current interrupting at full rated current

Environmental Specifications	
Flammability:	Rated V-2 per UL94
Operating Temperature:	-40C to 60C

Material Specifications	
Body Material:	Nylon
Blades/Contacts:	Brass
Assembly Screws:	Steel, Zinc Plated

Mechanical Specifications	
Product ID:	Ratings and NEMA I.D. permanently marked on device
Terminal Accom.:	18-10 AWG
Terminal ID:	Brass-Hot, Green-Ground, Silver-Neutral
Cord Range:	.250 - .656

Standards and Certifications	
NEMA:	WD-6
ANSI:	C-73
UL:	Listed
CSA C22.2 No. 42:	File LR-406
NOM:	057