

Specification of Crystal Unit

1	NDK PART NUMBER	NX2520SA-16.00000MHz-W1
2	CHIPSET MAKER	FREESCALE
3	APPLICATION	Wireless LAN, ZIGBEE
4	CHIPSET NAME	MC13192
5	Type	NX2520SA
6	Electrical characteristics	
6.1	Nominal frequency(F0)	16.000MHz
6.2	Overtone order	Fundamental
6.3	Adjustment tolerance	$\pm 20 \times 10^{-6}$ max. (+25 °C)
6.4	Tolerance over the temperature range	$\pm 20 \times 10^{-6}$ max. (-40~+85 °C) The reference temperature shall be +25 °C.
6.5	Equivalent resistance (R1)	120Ω max.
6.6	Shunt Capacitance (C0)	7.0 pF max.
6.7	Maximum Drive Level	200μW max.
7	Measurement circuit	
7.2	Frequency measurement	
7.1.1	Measuring instrument	π circuit
7.1.2	Load capacitance(CL)	8pF
7.1.3	Level of drive	50μW
7.2	Equivalent resistance measurement	
7.2.1	Measuring instrument	π circuit
7.2.2	Load capacitance(CL)	Series
7.2.3	Level of drive	50μW

8 Dimension

