


Front panels


Front panels, U profile, shieldable

2 HP

3 U



> 3 HP



- High stability through U profile
- Front panel, U profile, Al, front anodised, rear conductive, 2 alignment pins pressed-in, stainless steel
- Differences in the finish between 2 ... 12 HP and 14 ... 84 HP

Order Information

Height H	Width B	b1	b2	Align-	Qty	Part no.		
U mm	HP	mm	mm	ment				
				pin				
2	84	84	426.4	411.5	203.2	—	1 (SPQ 5) ¹⁾	20848-262
3	128.4	2	9.8	—	—	x	1 (SPQ 5) ¹⁾	30849-001
3	128.4	3	14.9	—	—	x	1 (SPQ 5) ¹⁾	30849-004
3	128.4	4	20	—	—	x	1 (SPQ 5) ¹⁾	30848-354
3	128.4	5	25	—	—	x	1 (SPQ 5) ¹⁾	30848-378
3	128.4	6	30.1	—	—	x	1 (SPQ 5) ¹⁾	30848-380
3	128.4	7	35.2	—	—	x	1 (SPQ 5) ¹⁾	30848-382
3	128.4	8	40.3	25.4	—	x	1 (SPQ 5) ¹⁾	30848-356
3	128.4	10	50.5	35.6	—	x	1 (SPQ 5) ¹⁾	30848-386
3	128.4	12	60.6	45.7	—	x	1 (SPQ 5) ¹⁾	30848-358
3	128.4	14	70.8	55.9	—	x	1 (SPQ 5) ¹⁾	20848-013
3	128.4	16	80.9	66	—	x	1 (SPQ 5) ¹⁾	20848-015
3	128.4	21	106.3	91.4	—	x	1 (SPQ 5) ¹⁾	20848-020
3	128.4	28	141.9	127	—	x	1 (SPQ 5) ¹⁾	20848-027
3	128.4	42	213	198.1	101.6	x	1	20848-047
3	128.4	63	319.7	304.8	157.5	x	1	20848-068
3	128.4	84	426.4	411.5	203.2	—	1	20848-097
4	172.9	84	426.4	411.5	203.2	—	1	20848-271
6	261.8	2	9.8	—	—	x	1 (SPQ 5) ¹⁾	30849-002
6	261.8	4	20	—	—	x	1 (SPQ 5) ¹⁾	30848-355
6	261.8	5	25	—	—	x	1 (SPQ 5) ¹⁾	30848-379
6	261.8	6	30.1	—	—	x	1 (SPQ 5) ¹⁾	30848-381
6	261.8	7	35.2	—	—	x	1 (SPQ 5) ¹⁾	30848-383
6	261.8	8	40.3	25.4	—	x	1 (SPQ 5) ¹⁾	30848-357
6	261.8	10	50.5	35.6	—	x	1 (SPQ 5) ¹⁾	30848-387
6	261.8	12	60.6	45.7	—	x	1 (SPQ 5) ¹⁾	30848-359
6	261.8	14	70.8	55.9	—	x	1 (SPQ 5) ¹⁾	20848-106
6	261.8	16	80.9	66	—	x	1 (SPQ 5) ¹⁾	20848-108
6	261.8	21	106.3	91.4	—	x	1 (SPQ 5) ¹⁾	20848-113
6	261.8	28	141.9	127	—	x	1 (SPQ 5) ¹⁾	20848-120
6	261.8	42	213	198.1	101.6	x	1	20848-139
6	261.8	63	319.7	304.8	157.5	x	1	20848-160
6	261.8	84	426.4	411.5	208.3	—	1	20848-189
9	395.1	84	426.4	411.5	203.2	—	1	20848-280

1) Delivery is exclusively made in Standard Pack Quantity (SPQ): Please order at least 5 pieces or a multiple.
Pricing is per individual item.

Note

- Differences in finish between 2 ... 12 HP and 14 ... 84 HP
 - 2 ... 12 HP: one-part U-profile
 - 14 ... 84 HP: multi-part U-profile (front panel with crimped profiles)
- Please order fixing material (sleeves, collar screws) separately, see page 7.107
- Please order textile EMC gasket separately, see page 7.6