






Fuse Holders

441-R359A-GR, 441-R359B-GR,
441-R359C-GR, 441-R359D-GR

Date Last Revised: 01-11-08



Dimensions: mm (in.)

Type	Wire	Rating	Wire Color
441-R359A-GR	12AWG	30A 12-24 VDC	Red
441-R359B-GR	14AWG	20A 12-24 VDC	Red
441-R359C-GR	16AWG	15A 12-24 VDC	Red
441-R359D-GR	18AWG	10A 12-24 VDC	Red

SPECIFICATIONS	
Rating:	12 - 24 VDC
Contact Resistance	50m Ω max.
Insulation Resistance:	500VDC 100M Ω min.
Dielectric Strength:	1000VAC, 1 minute
Body:	PVC
RoHS Compliant	

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

EPD-200531

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[441-R359A-GR](#) [441-R359B-GR](#) [441-R359D-GR](#) [441-R359C-GR](#)