





MOP450GA

Monochrome CMOS Camera With Microphone

High Quality Picture
Compact Size
Low Power Consumption
High Sensitivity
Microphone




Specifications:

Signal	CCIR (EIA available)
Sensor	1/3 Interline CMOS
Number of Pixels	352 X 288
Scanning	2:1 Interlace
Synchronisation	Internal
Resolution	240TV lines
Video Out Level	1.0Vp-p/75ohms composite
S/N	46dBMin.
Lens information	3.6mm/F2.0 92 degree
Minimum Illumination	1 Lux (f1.4)
Gamma Correction	0.45
Working temperature	-10 to 45 °C
Electrical Shutter	1/50 ~ 1/6000 Sec
Power Supply Voltage	DC12V
Power Supply Current	20mA Max.

Dimensions

RCA male yellow for video output
RCA male white for audio output



Input DC Plug Female For Power Input
Center(+),Outer(-)