


EPIC® Pin & Sleeve Connectors

20 Amp: North American Version
MULTIMAX with Cable Sleeve

IP 44



Technical Data

Impact Resistance:	8J
Ambient Temperature:	-25°C to 70°C
Flame Resistance:	
➤Glow Wire Test: Enclosure:	850°C
➤Glow Wire Test: Contact Enclosure:	850°C
➤Self-Extinguishing: Enclosure:	UL94-V2
➤Self-Extinguishing: Contact Carrier:	UL94-V2

Part Numbers

Part Number	Voltage	# of Wires	# of Poles	Ground-Clock Position
720124FX	125	3	1+N+PE	4
720126FX	250	3	2+PE	6
720127FX	480	3	2+PE	7
721132FX	125/250	4	2+N+PE	12
720139FX	3Ø250	4	3+PE	9
720137FX	3Ø480	4	3+PE	7
720135FX	3Ø600	4	3+PE	5
720149FX	3ØY 120/208	5	3+N+PE	9
720147FX	3ØY 277/480	5	3+N+PE	7
720145FX	3ØY 347/600	5	3+N+PE	5