

ABF.00.250.NTA
Status Active

Size/Series 00 / 00

[Request a quote](#)
MECHANICAL DETAILS

Shell Style/Model ABF*: Adapter from LEMO plug to BNC receptacle

Keying Circular (can rotate)

Housing Material Brass (nickel plated) shell, collet nut, latch sleeve and mid pieces

Cable Fixing J : 0 - 0 mm

Variant :

	A	L	M	Weight
mm.	11.5	36	28	8.3
in.	0.45	1.42	1.10	0.33

PERFORMANCE DETAILS

Insert Configuration 0.25 : 1 Coax (50 Ohm)

Insulator T: PTFE

Specifications

Contact Type: Coaxial 50 Ohm

Max. Matings: 500

Contact Dia.: 0.7 mm (0.03in)

OTHER CHARACTERISTICS

Endurance (Shell) 5000 mating cycles

F ret (min): 100 N

IP Rating 50

Catalog

