

Offset screwdriver



207 Slotted offset screwdriver, with handle, DIN 5200.

For working in confined spaces.

Blade chrome-vanadium-molybdenum-special-steel, hardened, chrome-plated.

Handle high quality plastic, impact resistant, black, cadmium free.

3,5	90	8,5	0,6	3,5	12	10
4,0	100	9,0	0,8	4,0	15	10
5,5	125	10,5	1,0	5,5	32	10
6,5 +	125	13,5	1,2	6,5	42	10
8,0	150	17,0	1,2	8,0	71	10
10,0	175	24,0	1,6	9,0	111	10
12,0	200	27,0	2,0	10,0	156	5

Ref.-No.

00373

00374

00375

00376

00377

00378

00379

+ Additional sizes to DIN dimensions.



161 Phillips offset screwdriver, with handle, DIN 5208.

For working in confined spaces.

Blade chrome-vanadium-molybdenum-special-steel, hardened, chrome-plated.

Handle high quality plastic, impact resistant, black, cadmium free.

1 + 2	125	14,5	5,5	27	10
2 + 3	150	21,0	8,0	76	10
3 + 4	200	25,0	10,0	160	10

Ref.-No.

00144

00145

00146



224 Pozidriv-Supadriv offset screwdriver, with handle.

For working in confined spaces.

Blade chrome-vanadium-molybdenum-special-steel, hardened, black finish.

Handle high quality plastic, impact resistant, black, cadmium free.

1 + 2	125	14,5	5,5	27	10
2 + 3	150	21,0	8,0	76	10
3 + 4	200	25,0	10,0	160	10


Ref.-No.

00432

00433

00434

Screw-holding drivers



390 Slotted screw-holding screwdriver, with Wiha-square handle.

Split blade to hold screw.

Blade chrome-vanadium-steel, hardened, galvanized.

Sliding sleeve.

Wiha-square handle cellulose-acetate, impact resistant, red transparent, cadmium free.

0,4	5,0	90	175	85	22	46	5
0,4	5,0	215	300	85	22	66	5
0,6	3,5	125	220	95	24	78	5
0,6	3,5	175	270	95	24	91	5
0,6	3,5	225	320	95	24	105	5
0,6	5,5	125	220	95	24	78	5
0,6	5,5	175	270	95	24	82	5
0,6	5,5	225	320	95	24	102	5
0,8	5,5	130	225	95	24	85	5
0,8	5,5	180	275	95	24	99	5
0,8	5,5	230	325	95	24	112	5
1,2	8,0	190	295	105	28	135	5
1,2	8,0	235	340	105	28	155	5

Ref.-No.

01483

01484

01485

01486

01487

01488

01489

01490


01491

01492

01493

01494

01495



394 Slotted screw-holding screwdriver, with Wiha-square handle.

Clamping sleeve to hold screw.

Blade chrome-vanadium-molybdenum-steel, hardened, black finish, clamping sleeve polyamide.

Wiha-square handle cellulose-acetate, impact resistant, red, cadmium free.

2,5	75	160	85	22	36	5
3,0	100	195	95	24	56	5
4,0	125	230	105	28	85	5
5,0	150	265	115	32	122	5
6,0	175	290	115	32	145	5

Ref.-No.

01496

01497

01498

01499

01500