


G23 Lampholders

**Type: 35006****Item number: 101306**

Fatigue-free stainless lamp carrier
spring
Central fixing hole for screw M3
If the central hole is used, make sure
there is no risk of torsion


Lamp base: G23
Material: PBT GF
Colour: White
Fixing: Base fixing holes for
screws M4
Starter: No
Connection: Push-in twin terminal
0,5-1mm²
Lamp axis [mm]: 17,5
T-Marking: 140
IP degree of
protection: 20
Nominal rating: 2 A/250 V



Unit: 500 pcs.

For a large drawing of **item 101306**
please click on the thumbnail-picture:

Received
approbations: **VDE-ENEC , UL-
CSA-46U4**

[Print Data Sheet](#)

If you want to use all features of this site you must log on. If this is your
first visit at the Vossloh Schwabe Web site please register now.

[Log In](#)[Registration](#)[Back](#)