




710-118 & 710-120 Metal Split "Y" and "T" Transitions for Series 72 & 74 Tubing and Series 75 Conduit

710 - 118 M A24 B08 C16
 Product Series —————
 Basic Part Number: —————
 118 = Aluminum "Y" Transition
 120 = Aluminum "T" Transition
 —————"A" - End Conduit Dash No.
 —————"B" - End Conduit Dash No.
 —————"C" - End Conduit Dash No.
 —————Finish (Table II)



Glenair also offers numerous other "Y" and "T" fitting designs not presented in this catalog. Consult the factory for your specific requirements.

710-118 & 710-120
Metal Split "Y" and "T" Transitions
for Series 72 & 74 Tubing and Series 75 Conduit



TABLE I

CONDUIT DASH NO.	E MAX	F MAX	G MAX	H THREAD CLASS 2A
06	1.850 (47.0)	1.625 (41.3)	3.250 (82.6)	7/16 - 28 UNEF
08	1.850 (47.0)	1.625 (41.3)	3.250 (82.6)	1/2 - 20 UNF
09	1.850 (47.0)	1.625 (41.3)	3.250 (82.6)	9/16 - 24 UNEF
10	1.850 (47.0)	1.625 (41.3)	3.250 (82.6)	9/16 - 24 UNEF
12	1.850 (47.0)	1.625 (41.3)	3.250 (82.6)	5/8 - 24 UNEF
14	1.850 (47.0)	1.625 (41.3)	3.250 (82.6)	11/16 - 24 UNEF
16	1.850 (47.0)	1.625 (41.3)	3.250 (82.6)	3/4 - 20 UNEF
20	2.038 (51.8)	1.750 (44.5)	3.500 (88.9)	7/8 - 20 UNEF
24	2.038 (51.8)	1.750 (44.5)	3.500 (88.9)	1 - 20 UNEF
28	2.475 (62.9)	1.875 (47.6)	3.750 (95.3)	1 3/16 - 18 UNEF
32	2.475 (62.9)	1.875 (47.6)	3.750 (95.3)	1 5/16 - 18 UNEF
40	2.725 (69.2)	2.000 (50.8)	4.000 (101.6)	1 1/2 - 18 UNEF
48	3.288 (83.5)	2.312 (58.7)	4.625 (117.5)	1 3/4 - 18 UNS

TABLE II

SYMBOL	FINISH
B	Olive Drab over Cadmium Plate
J	Gold Iridite over Cadmium Plate over Nickel
M	Electroless Nickel
N	Olive Drab over Cadmium Plate over Nickel
NC	Zinc-Cobalt, Olive Drab
NF	Olive Drab over Cadmium Plate over Electroless Nickel (500 Hour Salt Spray)
T	Bright Dip Cadmium Plate over Nickel

Overall dimensions will be determined by largest conduit dash number ordered
(e.g. 710-118MA20B12C32 will have dash number 32 dimensions).

Metric dimensions (mm) are in parentheses.