

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

G

14



F

REV PER 0G3A-0092-03

03FEB03

JR

TM

AMP
WIRE RANGEFILE
E66717LR7189
Certified16-14 AWG
STRANDED16-14 AWG
STRANDED16-14 AWG
STRANDED

1 MARKED AMP 16-14

2 DESIGNED FOR WIRE
INSULATION DIA OF
.110-.165.3 MATES WITH .250±.003
BY .032±.001 THK TAB.4 BODY: BRASS, TIN PLATED
SLEEVE: VINYL, BLUE

5 RATED FOR 15 MAX AMPERE

100

LOOSE PIECE

8-696302-1

3500

ON TAPE

696302-2

1000

LOOSE PIECE

696302-1

QTY

PACKAGE TYPE

PART NO.


TYCO ELECTRONICS
CUSTOMER SERVICE SYSTEMFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWING
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
75°C [167°F]VOLTAGE RATING:
300V MAXCIRCULAR MIL AREA:
2,050-5,180
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

- 4

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .008
4 PLC ± -
ANGLES ± -
FINISH - 4

DWN JR RUTH 15MAR01

CHK MS FEHER 15MAR01

APVD T MICHIELUTTI 15MAR01

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, PA. 17057NAME
RECEPTACLE, 250 SERIES, FASTON, BUDGET,
PRE-INSULATED, WIRE:16-14 AWG

SIZE A3 CAGE CODE 00779 DRAWING NO C-696302 RESTRICTED TO -

SCALE 4:1

SHEET 1 OF 1

REV F