




4. MODULAR PLUG ASSEMBLY
SHIELDED RJ-45 8P8C
WITH 50 MICRO INCH GOLD PLATING
WITH S/R BOOT
3. REFER TO PS-83421-9000 FOR PRODUCT SPEC.
2. MICRO-D, 9 SOCKET FEMALE CONNECTOR (CRIMP TYPE)
CONTACTS: BRASS ALLOY, 30 MICRO INCH GOLD PLATED.
INSULATOR: PVC OVERMOLD, COLOR: BLACK.
WITH (2) #2-56 JACKSCREWS

1. CABLE: CAT 5E 26AWG 4 PAIR & DRAIN WIRE
8 CONDUCTOR, TINNED COPPER, 7 STRAND.
WIRE INSULATION: PVC
SHIELD: AL-FOIL/MYLAR. INCLUDING DRAIN WIRE & BRAID
OUTER CABLE JACKET: BLACK PVC.

NOTES: UNLESS OTHERWISE SPECIFIED.

RESTRICTED SALES DRAWING

CHNG TO SD IN MIDAS EC NO. ETC2004-0077 DRWN: EMF 03/09/26 CHK: HEB 03/09/26 APPR: RSD 03/09/26 A I	DESCRIPTION REV	QUALITY SYMBOLS MAJOR =0 CRITICAL =0	GENERAL TOLERANCES: (UNLESS SPECIFIED)			SCALE NO:NE	DESIGN UNITS ☐ mm ☒ INCH	THIRD ANGLE PROJECTION	DIMENSIONS: ☐ mm ☒ INCH INCH mm ONLY			SHT	REV				
									REVISE ON CAD ONLY								
						DRAWN BY & DATE JAL 03/04/07			TITLE: CABLE ASSEMBLY 9 SKT MICRO D TO 8 POS. MOD. PLUG ASSY W/OVERMOLD								
						CHECKED BY & DATE / /											
						APPROVED BY & DATE RWD 03/04/10										MOLEX INCORPORATED	
						CAD FILENAME RSD-83421-024DGN			MATERIAL NO. SEE CHART	DRAWING NO. RSD-83421-024	SHEET NO. 1 OF 1						
						ANGULAR: ±2 °			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.								
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										SIZE B	