

AV2510E712Q04

✓ ACTIVE

ALCOSWITCH | ALCOSWITCH AV25


TE Internal #: 2317656-9

Anti-Vandal Switch, Single Pole - Single Throw Configuration (Pole-Throw), Single Actuator, Flush Actuator, Illuminated, ALCOSWITCH AV25

[View on TE.com >](#)



Switches > Push Button Switches



Configuration (Pole-Throw): **Single Pole - Single Throw**

Push Button Switch Product Type: **Anti-Vandal Switch**

Number of Actuators: **Single**

Actuator Profile: **Flush**

Bushing Style: **Threaded**

Features

Product Type Features

Switch Connection Type	Wire Lugs
Push Button Switch Product Type	Anti-Vandal Switch
Illuminated	With
Actuator Style	Round Actuator

Configuration Features

Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Switch Feedback Type	Auditory
Operating Function	Momentary

Electrical Characteristics

Contact Current Rating	3 A
Operating Voltage Range	250 VAC



Body Features

Case Material	PBT
Product Orientation	Vertical
Actuator Force	255 g[9 oz]
Actuator Profile	Flush
Bushing Style	Threaded

Contact Features

Contact Base Material	Copper
Switch Contact Plating Material	Silver

Housing Features

Process Sealed	Yes
----------------	-----

Industry Standards

IP Rating	IP67
-----------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

















Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products




will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 2317656-4 AV25 SPM 3A MOVING RING RED 24V	 TE Part # 1-2317656-4 AV25 SPL 3A MOVING RING RED 24V	 TE Part # 2-2317656-4 AV25 DPM 3A MOVING RING RED 24V	 TE Part # 2317657-7 AV25 SPL 3A MOVING RING R&B 12V FL
 TE Part # 2317657-8 AV25 SPL 3A MOVING RING R&B 24V FL	 TE Part # 3-2317656-4 AV25 DPL 3A MOVING RING RED 24V	 TE Part # 2317657-4 AV25 SPM 3A MOVING RING R&B 24V FL	 TE Part # 2317659-4 AV25 SPM 3A MOVING RING POWER R&B 24V FL
 TE Part # 2-2317656-6 AV25 DPM 3A MOVING RING YELLOW 24V	 TE Part # 3-2317656-6 AV25 DPL 3A MOVING RING YELLOW 24V	 TE Part # 1-2317659-2 AV25 DPM 3A MOVING RING POWER R&B 24V FL	 TE Part # 1-2317656-6 AV25 SPL 3A MOVING RING YELLOW 24V
 TE Part # 3-2317656-1 AV25 DPL 3A MOVING RING WHITE 12V	 TE Part # 2328820-1 AV 25 SPM 3A MOVING RING R&G 12V	 TE Part # 2-2317656-1 AV25 DPM 3A MOVING RING WHITE 12V	 TE Part # 2-2317656-5 AV25 DPM 3A MOVING RING YELLOW 12V







TE Part # 3-2317656-7
AV25 DPL 3A MOVING RING GREEN 12V



TE Part # 3-2317656-3
AV25 DPL 3A MOVING RING RED 12V



TE Part # 2-2317658-8
AV25 DPL 3A MOVING RING POWER YELLOW 24V



TE Part # 2317655-2
AV25 SPL 3A NO LED FL

Also in the Series

ALCOSWITCH AV25



Anti-Vandal Switches(88)



Push Button Switches(88)

Customers Also Bought



TE Part #CJ4552-000
D-141-30-LF



TE Part #CP2527-000
RT-780-3/8-3-SP



TE Part #41202
250 FASTON,REC.,18-14 AWG,BR



TE Part #41274
250 FASTON,REC.,18-14 AWG,TPBR



TE Part #3-350566-1
MINI AMP-IN 22-18 PTLP/PHBZ



TE Part #640456-9
09P MTA100 HDR ASSY F/L SQ STR




TE Part #3-643813-9
09P MTA100 CONN ASSY POL RIB



TE Part #3-643819-4
04P MTA156 CONN ASSY 22AWG RED



TE Part #1969608-4
4P VAL-U-LOK TPA 22-18 AWG



TE Part #2213771-1
AV22 SPM 3A NO LED



Documents

Product Drawings

AV25 SPM 3A MOVING RING BLUE 12V

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2317656-9_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2317656-9_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2317656-9_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ALCOSWITCH Anti-Vandal Switch

English

Agency Approvals

UL Report

English