

Datasheet

Item No. 70.353.2435.0

Hood BAS GOT GA 24 M32 50 A0

revos BASIC 500V size 24 hood with cable gland M32, lateral cable entry, double locking lever



Item No.	70.353.2435.0
EAN	4015573651722
order unit	1 Piece(s)

Approvals



Technical data

General

Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	24
Model	Plug
Locking mechanism	Double locking levers
Cable entry	Sideways
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	32
Hinged lid	No
EMC-version	No

Drawings

