




13			12		11		10		9		8		7		6		5		4		3		2		1			
PACKAGING SEE NOTE 4 SHT 1			4-6 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A				BULK		BULK	
			8-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS				TUBES		TUBES	
			DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)				8.13 (.320)	
			PLATING				150 TIN				15 GOLD				30 GOLD								15 GOLD				30 GOLD	
			DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)				4.57 (.180)	
CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS	
	MM	IN	MM	IN																								
04	5.08	.200	2.54	.100	015-91-2040	015-91-6040	N/A	015-91-0040	015-91-6042	N/A	015-91-3040	015-91-6043	N/A		015-91-0048	015-91-5049	04											
06	7.62	.300	5.08	.200	015-91-2060	015-91-6060	N/A	015-91-0060	015-91-6062	N/A	015-91-3060	015-91-6063	N/A		015-91-0068	015-91-5069	06											
08	10.16	.400	7.62	.300	015-91-2080	015-91-6080	015-91-3087	015-91-0080	015-91-6082	015-91-3086	015-91-3080	015-91-6083	015-91-3088		015-91-0088	015-91-5089	08											
10	12.70	.500	10.16	.400	015-91-2100	015-91-6100	015-91-3107	015-91-0100	015-91-6102	015-91-3106	015-91-3100	015-91-6103	015-91-3108		015-91-0108	015-91-5109	10											
12	15.24	.600	12.70	.500	015-91-2120	015-91-6120	015-91-3127	015-91-0120	015-91-6122	015-91-3126	015-91-3120	015-91-6123	015-91-3128		015-91-0128	015-91-5129	12											
14	17.78	.700	15.24	.600	015-91-2140	015-91-6140	015-91-3147	015-91-0140	015-91-6142	015-91-3146	015-91-3140	015-91-6143	015-91-3148		015-91-0148	015-91-5149	14											
16	20.32	.800	17.78	.700	015-91-2160	015-91-6160	015-91-3167	015-91-0160	015-91-6162	015-91-3166	015-91-3160	015-91-6163	015-91-3168		015-91-0168	015-91-5169	16											
18	22.86	.900	20.32	.800	015-91-2180		015-91-3187	015-91-0180		015-91-3186	015-91-3180		015-91-3188		015-91-0188	015-91-5189	18											
20	25.40	1.000	22.86	.900	015-91-2200	015-91-6200	015-91-3207	015-91-0200	015-91-6202	015-91-3206	015-91-3200	015-91-6203	015-91-3208		015-91-0208	015-91-5209	20											
22	27.94	1.100	25.40	1.000	015-91-2220		015-91-3227	015-91-0220		015-91-3226	015-91-3220		015-91-3228		015-91-0228	015-91-5229	22											
24	30.48	1.200	27.94	1.100	015-91-2240		015-91-3247	015-91-0240		015-91-3246	015-91-3240		015-91-3248		015-91-0248	015-91-5249	24											
26	33.02	1.300	30.48	1.200	015-91-2260	015-91-6260	015-91-3267	015-91-0260	015-91-6262	015-91-3266	015-91-3260		015-91-3268		015-91-0268	015-91-5269	26											
28	35.56	1.400	33.02	1.300	015-91-2280		015-91-3287	015-91-0280		015-91-3286	015-91-3280		015-91-3288		015-91-0288	015-91-5289	28											
30	38.10	1.500	35.56	1.400	015-91-2300		015-91-3307	015-91-0300		015-91-3306	015-91-3300		015-91-3308		015-91-0308	015-91-5309	30											
32	40.64	1.600	38.10	1.500	015-91-2320		015-91-3327	015-91-0320		015-91-3326	015-91-3320		015-91-3328		015-91-0328	015-91-5329	32											
34	43.18	1.700	40.64	1.600	015-91-2340		015-91-3347	015-91-0340		015-91-3346	015-91-3340		015-91-3348		015-91-0348	015-91-5349	34											
36	45.72	1.800	43.18	1.700	015-91-2360		015-91-3367	015-91-0360		015-91-3366	015-91-3360		015-91-3368		015-91-0368	015-91-5369	36											
38	48.26	1.900	45.72	1.800	015-91-2380		015-91-3387	015-91-0380		015-91-3386	015-91-3380		015-91-3388		015-91-0388	015-91-5389	38											
40	50.80	2.000	48.26	1.900	015-91-2400	015-91-6400	015-91-3407	015-91-0400	015-91-6402	015-91-3406	015-91-3400	015-91-6403	015-91-3408		015-91-0408	015-91-5409	40											
42	53.34	2.100	50.80	2.000	015-91-2420		015-91-3427	015-91-0420		015-91-3426	015-91-3420		015-91-3428		015-91-0428	015-91-5429	42											
44	55.88	2.200	53.34	2.100	015-91-2440		015-91-3447	015-91-0440		015-91-3446	015-91-3440		015-91-3448		015-91-0448	015-91-5449	44											
46	58.42	2.300	55.88	2.200	015-91-2460		015-91-3467	015-91-0460		015-91-3466	015-91-3460		015-91-3468		015-91-0468	015-91-5469	46											
48	60.96	2.400	58.42	2.300	015-91-2480		015-91-3487	015-91-0480		015-91-3486	015-91-3480		015-91-3488		015-91-0488	015-91-5489	48											
50	63.50	2.500	60.96	2.400	015-91-2500	015-91-6500	015-91-3507	015-91-0500	015-91-6502	015-91-3506	015-91-3500	015-91-6503	015-91-3508		015-91-0508	015-91-5509	50											
52	66.04	2.600	63.50	2.500	015-91-2520		015-91-3527	015-91-0520		015-91-3526	015-91-3520		015-91-3528		015-91-0528	015-91-5529	52											
54	68.58	2.700	66.04	2.600	015-91-2540		015-91-3547	015-91-0540		015-91-3546	015-91-3540		015-91-3548		015-91-0548	015-91-5549	54											
56	71.12	2.800	68.58	2.700	015-91-2560		015-91-3567	015-91-0560		015-91-3566	015-91-3560		015-91-3568		015-91-0568	015-91-5569	56											
58	73.66	2.900	71.12	2.800	015-91-2580		015-91-3587	015-91-0580		015-91-3586	015-91-3580		015-91-3588		015-91-0588	015-91-5589	58											
60	76.20	3.000	73.66	2.900	015-91-2600		015-91-3607	015-91-0600		015-91-3606	015-91-3600		015-91-3608		015-91-0608	015-91-5609	60											
62	78.74	3.100	76.20	3.000	015-91-2620		015-91-3627	015-91-0620		015-91-3626	015-91-3620		015-91-3628		015-91-0628	015-91-5629	62											
64	81.28	3.200	78.74	3.100	015-91-2640		015-91-3647	015-91-0640		015-91-3646	015-91-3640		015-91-3648		015-91-0648	015-91-5649	64											
66	83.82	3.300	81.28	3.200	015-91-2660		015-91-3667	015-91-0660		015-91-3666	015-91-3660		015-91-3668		015-91-0668	015-91-5669	66											
68	86.36	3.400	83.82	3.300	015-91-2680		015-91-3687	015-91-0680		015-91-3686	015-91-3680		015-91-3688		015-91-0688	015-91-5689	68											
70	88.90	3.500	86.36	3.400	015-91-2700		015-91-3707	015-91-0700		015-91-3706	015-91-3700		015-91-3708		015-91-0708	015-91-5709	70											
72	91.44	3.600	88.90	3.500	015-91-2720		015-91-3727	015-91-0720		015-91-3726	015-91-3720		015-91-3728		015-91-0728	015-91-5729	72											
74	93.98	3.700	91.44	3.600	015-91-2740		015-91-3747	015-91-0740		015-91-3746	015-91-3740		015-91-3748		015-91-0748	015-91-5749	74											
76	96.52	3.800	93.98	3.700	015-91-2760		015-91-3767	015-91-0760		015-91-3766	015-91-3760		015-91-3768		015-91-0768	015-91-5769	76											
78	99.06	3.900	96.52	3.800	015-91-2780		015-91-3787	015-91-0780		015-91-3786	015-91-3780		015-91-3788		015-91-0788	015-91-5789	78											
80	101.60	4.000	99.06	3.900	015-91-2800		015-91-3807	015-91-0800		015-91-3806	015-91-3800		015-91-3808		015-91-0808	015-91-5809	80											
82	104.14	4.100	101.60	4.000	71308-0082		71308-0482	71308-0182		71308-0582	71308-0282		71308-0682		71308-1182	71308-1282	82											
84	106.68	4.200	104.14	4.100	71308-0084		71308-0484	71308-0184		71308-0584	71308-0284		71308-0684		71308-1184	71308-1284	84											
86	109.22	4.300	106.68	4.200	71308-0086		71308-0486	71308-0186		71308-0586	71308-0286		71308-0686		71308-1186	71308-1286	86											
88	111.76	4.400	109.22	4.300	71308-0088		71308-0488	71308-0188		71308-0588	71308-0288		71308-0688		71308-1188	71308-1288	88											
90	114.30	4.500	111.76	4.400	71308-0090		71308-0490	71308-0190		71308-0590	71308-0290		71308-0690		71308-1190	71308-1290	90											
92	116.84	4.600	114.30	4.500	71308-0092		71308-0492	71308-0192		71308-05																		

13		12		11				10		8		7		6		5		4		3		2		1					
J		IN TAPE AND REEL WITH SHALLOW POCKET TAPE										BULK / IN TUBES										J							
		PACKAGING SEE NOTE 4. SHT 1		4-8 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										BULK		BULK									
				10-100 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										TUBES		TUBES									
		DIM. M±0.25 MM				6.10 (.240)		6.10 (.240)										8.13 (.320)		13.59 (.535)									
		PLATING				30 GOLD		15 GOLD										150 TIN		150 TIN									
		DIM. H				2.54 (.100)		2.54 (.100)										4.57 (.180)		4.57 (.180)									
I		CKTS		DIM. A		DIM. B		EDP NUMBER		EDP NUMBER								EDP NUMBER		EDP NUMBER		CKTS							
				MM IN		MM IN																							
H		04	5.08	.200	2.54	.100																	04						
		06	7.62	.300	5.08	.200			015-91-6068														06						
		08	10.16	.400	7.62	.300			015-91-6088																08				
		10	12.70	.500	10.16	.400			015-91-6108										713088010		71308-8210				10				
		12	15.24	.600	12.70	.500																			12				
		14	17.78	.700	15.24	.600	015-91-6148																		14				
		16	20.32	.800	17.78	.700													713088016						16				
		18	22.86	.900	20.32	.800																			18				
		20	25.40	1.000	22.86	.900																			20				
		22	27.94	1.100	25.40	1.000																			22				
G		24	30.48	1.200	27.94	1.100																			24				
		26	33.02	1.300	30.48	1.200																			26				
		28	35.56	1.400	33.02	1.300																			28				
		30	38.10	1.500	35.56	1.400																			30				
		32	40.64	1.600	38.10	1.500																			32				
		34	43.18	1.700	40.64	1.600																			34				
		36	45.72	1.800	43.18	1.700																			36				
		38	48.26	1.900	45.72	1.800																			38				
		40	50.80	2.000	48.26	1.900																			40				
		42	53.34	2.100	50.80	2.000																			42				
F		44	55.88	2.200	53.34	2.100																			44				
		46	58.42	2.300	55.88	2.200																			46				
		48	60.96	2.400	58.42	2.300																			48				
		50	63.50	2.500	60.96	2.400																			50				
		52	66.04	2.600	63.50	2.500																			52				
		54	68.58	2.700	66.04	2.600																			54				
		56	71.12	2.800	68.58	2.700																			56				
		58	73.66	2.900	71.12	2.800																			58				
		60	76.20	3.000	73.66	2.900																			60				
		62	78.74	3.100	76.20	3.000																			62				
E		64	81.28	3.200	78.74	3.100																			64				
		66	83.82	3.300	81.28	3.200																			66				
		68	86.36	3.400	83.82	3.300																			68				
		70	88.90	3.500	86.36	3.400																			70				
		72	91.44	3.600	88.90	3.500																			72				
		74	93.98	3.700	91.44	3.600																			74				
		76	96.52	3.800	93.98	3.700																			76				
		78	99.06	3.900	96.52	3.800																			78				
		80	101.60	4.000	99.06	3.900																			80				
		82	104.14	4.100	101.60	4.000																			82				
D		84	106.68	4.200	104.14	4.100																			84				
		86	109.22	4.300	106.68	4.200																			86				
		88	111.76	4.400	109.22	4.300																			88				
		90	114.30	4.500	111.76	4.400																			90				
		92	116.84	4.600	114.30	4.500																			92				
		94	119.38	4.700	116.84	4.600																			94				
		96	121.92	4.800	119.38	4.700																			96				
		98	124.46	4.900	121.92	4.800																			98				
		100	127.00	5.000	124.46	4.900																			100				
		B		NO PEG VERSION (ALSO SEE SHEET 2)										SEE SHEET 1 EC NO: UCP2014-0809 DRAWN:KIPPER 2013/08/20 CHKD:JBELL 2013/08/20 APPR:FSMITH 2013/09/03 REV		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE MM/IN				SCALE		DESIGN UNITS INCH	
mm																		INCH		DRAWN BY DATE		TITLE							
4 PLACES ± ---																		± ---		KMS 1999/10/15		SALES ASSY INSULATOR							
3 PLACES ± ---																		± .005		CHECKED BY DATE		DUAL ROW SMT W/BREAK-OFF							
2 PLACES ± 0.13																		± .010		KMS 1999/10/15		.025SQ PIN GULLWING .100							
1 PLACE ± 0.25																		± ---		APPROVED BY DATE		molex							
0 PLACE ± ---		± ---		KMS 1999/10/15		DOCUMENT NO.		SD-71308-001		SHEET NO.																			
						SEE TABLE				3 OF 6																			
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
1b_frame_C_P_AM.T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1					

13			12		11		10		9		8	7	6	5	4	3	2		1							
			PACKAGING SEE NOTE 4 SHT 1		4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		BULK		BULK			
					DIM. M±0.25 MM		6.10 (.240)		6.10 (.240)		6.10 (.240)		8.13 (.320)		8.13 (.320)		8.13 (.320)									
					PLATING		150 TIN		15 GOLD		30 GOLD		150 TIN		15 GOLD		30 GOLD									
					DIM. H		2.54 (.100)		2.54 (.100)		2.54 (.100)		4.57 (.180)		4.57 (.180)		4.57 (.180)									
CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS			
	MM	IN	MM	IN	MM	IN																				
04	5.08	.200	2.54	.100	----	----	015-91-1041	015-91-6044	015-91-1042	015-91-6045	015-91-1043	015-91-6046	015-91-1044	015-91-0047	015-91-1040							04				
06	7.62	.300	5.08	.200	2.54	.100	015-91-1061	015-91-6064	015-91-1062	015-91-6065	015-91-1063	015-91-6066	015-91-1064	015-91-0067	015-91-1060							06				
08	10.16	.400	7.62	.300	5.08	.200	015-91-1081	015-91-6084	015-91-1082	015-91-6085	015-91-1083	015-91-6086	015-91-1084	015-91-0087	015-91-1080							08				
10	12.70	.500	10.16	.400	7.62	.300	015-91-1101	015-91-6104	015-91-1102	015-91-6105	015-91-1103	015-91-6106	015-91-1104	015-91-0107	015-91-1100							10				
12	15.24	.600	12.70	.500	10.16	.400	015-91-1121		015-91-1122		015-91-1123		015-91-1124	015-91-0127	015-91-1120							12				
14	17.78	.700	15.24	.600	12.70	.500	015-91-1141	015-91-6144	015-91-1142	015-91-6145	015-91-1143	015-91-6146	015-91-1144	015-91-0147	015-91-1140							14				
16	20.32	.800	17.78	.700	15.24	.600	015-91-1161	015-91-6164	015-91-1162	015-91-6165	015-91-1163	015-91-6166	015-91-1164	015-91-0167	015-91-1160							16				
18	22.86	.900	20.32	.800	17.78	.700	015-91-1181		015-91-1182		015-91-1183		015-91-1184	015-91-0187	015-91-1180							18				
20	25.40	1.000	22.86	.900	20.32	.800	015-91-1201		015-91-1202		015-91-1203		015-91-1204	015-91-0207	015-91-1200							20				
22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1221		015-91-1222		015-91-1223		015-91-1224	015-91-0227	015-91-1220							22				
24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1241	71308-6901	015-91-1242		015-91-1243		015-91-1244	015-91-0247	015-91-1240							24				
26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1261		015-91-1262		015-91-1263		015-91-1264	015-91-0267	015-91-1260							26				
28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1281		015-91-1282		015-91-1283		015-91-1284	015-91-0287	015-91-1280							28				
30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1301		015-91-1302		015-91-1303		015-91-1304	015-91-0307	015-91-1300							30				
32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1321		015-91-1322		015-91-1323		015-91-1324	015-91-0327	015-91-1320							32				
34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1341		015-91-1342		015-91-1343		015-91-1344	015-91-0347	015-91-1340							34				
36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1361		015-91-1362		015-91-1363		015-91-1364	015-91-0367	015-91-1360							36				
38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1381		015-91-1382		015-91-1383		015-91-1384	015-91-0387	015-91-1380							38				
40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1401		015-91-1402		015-91-1403		015-91-1404	015-91-0407	015-91-1400							40				
42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1421		015-91-1422		015-91-1423		015-91-1424	015-91-0427	015-91-1420							42				
44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1441		015-91-1442		015-91-1443		015-91-1444	015-91-0447	015-91-1440							44				
46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1461		015-91-1462		015-91-1463		015-91-1464	015-91-0467	015-91-1460							46				
48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1481		015-91-1482		015-91-1483		015-91-1484	015-91-0487	015-91-1480							48				
50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1501	015-91-6504	015-91-1502	015-91-6505	015-91-1503	015-91-6506	015-91-1504	015-91-0507	015-91-1500							50				
52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1521		015-91-1522		015-91-1523	71308-5203	015-91-1524	015-91-0527	015-91-1520							52				
54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1541		015-91-1542		015-91-1543		015-91-1544	015-91-0547	015-91-1540							54				
56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1561		015-91-1562		015-91-1563		015-91-1564	015-91-0567	015-91-1560							56				
58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1581		015-91-1582		015-91-1583		015-91-1584	015-91-0587	015-91-1580							58				
60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1601		015-91-1602		015-91-1603		015-91-1604	015-91-0607	015-91-1600							60				
62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1621		015-91-1622		015-91-1623		015-91-1624	015-91-0627	015-91-1620							62				
64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1641		015-91-1642		015-91-1643		015-91-1644	015-91-0647	015-91-1640							64				
66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1661		015-91-1662		015-91-1663		015-91-1664	015-91-0667	015-91-1660							66				
68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1681		015-91-1682		015-91-1683		015-91-1684	015-91-0687	015-91-1680							68				
70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1701		015-91-1702		015-91-1703		015-91-1704	015-91-0707	015-91-1700							70				
72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1721		015-91-1722		015-91-1723		015-91-1724	015-91-0727	015-91-1720							72				
74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1741		015-91-1742		015-91-1743		015-91-1744	015-91-0747	015-91-1740							74				
76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1761		015-91-1762		015-91-1763		015-91-1764	015-91-0767	015-91-1760							76				
78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1781		015-91-1782		015-91-1783		015-91-1784	015-91-0787	015-91-1780							78				
80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1801		015-91-1802		015-91-1803		015-91-1804	015-91-0807	015-91-1800							80				
82	104.14	4.100	101.60	4.000	99.06	3.900	71308-4082		71308-4182		71308-4282		71308-5082	71308-5182	71308-5282							82				
84	106.68	4.200	104.14	4.100	101.60	4.000	71308-4084		71308-4184		71308-4284		71308-5084	71308-5184	71308-5284							84				
86	109.22	4.300	106.68	4.200	104.14	4.100	71308-4086		71308-4186		71308-4286		71308-5086	71308-5186	71308-5286							86				
88	111.76	4.400	109.22	4.300	106.68	4.200	71308-4088		71308-4188		71308-4288		71308-5088	71308-5188	71308-5288							88				
90	114.30	4.500	111.76	4.400	109.22	4.300	71308-4090		71308-4190		71308-4290		71308-5090	71308-5190	71308-5290							90				
92	116.84	4.600	114.30	4.500	111.76	4.400	71308-4092		71308-4192		71308-4292		71308-5092	71308-5192	71308-5292							92				
94	119.38	4.700	116.84	4.600	114.30	4.500	71308-4094		71308-4194		71308-4294		71308-5094	71308-5194	71308-5294							94				
96	121.92	4.800	119.38	4.700	116.84	4.600	71308-4096		71308-4196		71308-4296		71308-5096	71308-5196	71308-5296							96				
98	124.46	4.900	121.92	4.800	119.38	4.700	71301																			

		13		12		11		10		9		8		7		6		5		4		3		2		1			
J				PACKAGING SEE NOTE 4 SHT 1		4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS															
						10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS															
						DIM. M±0.25 MM		6.10 (.240)		6.10 (.240)																			
						PLATING		30 GOLD		150 TIN																			
						DIM. H		2.54 (.100)		2.54 (.100)																			
I		CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		CKTS		
			MM	IN	MM	IN	MM	IN																					
		04	5.08	.200	2.54	.100	----	----	015-91-1048		015-91-6047																04		
		06	7.62	.300	5.08	.200	2.54	.100	015-91-1068		015-91-6067		71308-6106		71308-6206												06		
		08	10.16	.400	7.62	.300	5.08	.200	015-91-1088		015-91-6087		71308-6108		71308-6208												08		
		10	12.70	.500	10.16	.400	7.62	.300	015-91-1108		015-91-6107		71308-6110		71308-6210												10		
		12	15.24	.600	12.70	.500	10.16	.400	015-91-1128																		12		
		14	17.78	.700	15.24	.600	12.70	.500	015-91-1148		015-91-6147																14		
		16	20.32	.800	17.78	.700	15.24	.600	015-91-1168		015-91-6167																16		
		18	22.86	.900	20.32	.800	17.78	.700	015-91-1188																		18		
		20	25.40	1.000	22.86	.900	20.32	.800	015-91-1208		015-91-6207																20		
		22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1228																		22		
		24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1248																		24		
		26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1268				71308-6126														26		
		28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1288																		28		
		30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1308																		30		
		32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1328																		32		
		34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1348																		34		
		36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1368																		36		
		38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1388																		38		
		40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1408		015-91-6407																40		
		42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1428																		42		
		44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1448																		44		
		46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1468																		46		
		48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1488																		48		
		50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1508		015-91-6507																50		
		52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1528																		52		
		54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1548																		54		
		56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1568																		56		
		58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1588																		58		
		60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1608																		60		
		62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1628																		62		
		64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1648																		64		
		66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1668																		66		
		68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1688																		68		
		70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1708																		70		
		72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1728																		72		
		74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1748																		74		
		76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1768																		76		
		78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1788																		78		
		80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1808																		80		
		82	104.14	4.100	101.60	4.000	99.06	3.900	71308-6082																		82		
		84	106.68	4.200	104.14	4.100	101.60	4.000	71308-6084																		84		
		86	109.22	4.300	106.68	4.200	104.14	4.100	71308-6086																		86		
		88	111.76	4.400	109.22	4.300	106.68	4.200	71308-6088																		88		
		90	114.30	4.500	111.76	4.400	109.22	4.300	71308-6090																		90		
		92	116.84	4.600	114.30	4.500	111.76	4.400	71308-6092																		92		
		94	119.38	4.700	116.84	4.600	114.30	4.500	71308-6094																		94		
		96	121.92	4.800	119.38	4.700	116.84	4.600	71308-6096																		96		
		98	124.46	4.900	121.92	4.800	119.38	4.700	71308-6098																		98		
		100	127.00	5.000	124.46	4.900	121.92	4.800	71308-6100																		100		
B																													
A																													

		13		12		11		10		9		8		7		6		5		4		3		2		1					
J		PACKAGING SEE NOTE 4, SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/VAC CAPS		N/A		4-8 CKT		TAPE-N-REEL W/VAC CAPS		BULK		BULK		LONG PEG VERSION (.130")		SHORT PEG VERSION (.055")		BULK		TAPE-N-REEL W/ VAC CAPS					
						TUBES		TAPE-N-REEL W/VAC CAPS		TUBES W/ VAC CAPS				10-100 CKT		TAPE-N-REEL W/VAC CAPS		TUBES		TUBES		TUBES				TUBES				BULK	
				8-100 CKT																											
						DIM. M±0.25 MM				6.10 (.240)								8.13(.320)		13.59(.535)		6.10(.240)		8.13(.320)		6.10 (.240)					
				I		PLATING				59 TIN								59 TIN		59 TIN		59 TIN		59 TIN		59 TIN					
		DIM. H				2.54(.100)								4.57(.180)		4.57(.180)		2.54(.100)		4.57(.180)		2.54(.100)									
		KCTS		DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		KCTS			
				MM IN		MM IN		MM IN																							
				04		5.08 .200		2.54 .100		---		---		71308-5404		71308-5504		N/A				71308-6404		71308-6504		71308-6604		04			
				06		7.62 .300		5.08 .200		2.54 .100		---		71308-5406		71308-5506		N/A				71308-6406		71308-6506		71308-6606		06			
				08		10.16 .400		7.62 .300		5.08 .200		---		71308-5408		71308-5508		71308-5608				71308-6408		71308-6508		71308-6608		08			
				10		12.70 .500		10.16 .400		7.62 .300		---		71308-5410		71308-5510		71308-5610				71308-6410		71308-6510		71308-6610		10			
				12		15.24 .600		12.70 .500		10.16 .400		---		71308-5412		71308-5512		71308-5612				71308-6412		71308-6512		71308-6612		12			
				14		17.78 .700		15.24 .600		12.70 .500		---		71308-5414		71308-5514		71308-5614				71308-6414		71308-6514		71308-6614		14			
				16		20.32 .800		17.78 .700		15.24 .600		---		71308-5416		71308-5516		71308-5616				71308-6416		71308-6516		71308-6616		16			
				18		22.86 .900		20.32 .800		17.78 .700		---		71308-5418				71308-5618				71308-6418				71308-6618		18			
				20		25.40 1.000		22.86 .900		20.32 .800		---		71308-5420		71308-5520		71308-5620				71308-6420				71308-6620		20			
				22		27.94 1.100		25.40 1.000		22.86 .900		---		71308-5422				71308-5622				71308-6422				71308-6622		22			
				24		30.48 1.200		27.94 1.100		25.40 1.000		---		71308-5424				71308-5624		71308-5724		71308-6424				71308-6624		24			
				26		33.02 1.300		30.48 1.200		27.94 1.100		---		71308-5426				71308-5626				71308-6426				71308-6626		26			
				28		35.56 1.400		33.02 1.300		30.48 1.200		---		71308-5428				71308-5628				71308-6428				71308-6628		28			
				30		38.10 1.500		35.56 1.400		33.02 1.300		---		71308-5430				71308-5630				71308-6430				71308-6630		30			
				32		40.64 1.600		38.10 1.500		35.56 1.400		---		71308-5432				71308-5632				71308-6432				71308-6632		32			
				34		43.18 1.700		40.64 1.600		38.10 1.500		---		71308-5434				71308-5634				71308-6434				71308-6634		34			
				36		45.72 1.800		43.18 1.700		40.64 1.600		---		71308-5436				71308-5636				71308-6436				71308-6636		36			
				38		48.26 1.900		45.72 1.800		43.18 1.700		---		71308-5438				71308-5638				71308-6438				71308-6638		38			
				40		50.80 2.000		48.26 1.900		45.72 1.800		---		71308-5440		71308-5540		71308-5640				71308-6440				71308-6640		40			
				42		53.34 2.100		50.80 2.000		48.26 1.900		---		71308-5442				71308-5642				71308-6442				71308-6642		42			
				44		55.88 2.200		53.34 2.100		50.80 2.000		---		71308-5444				71308-5644				71308-6444				71308-6644		44			
				46		58.42 2.300		55.88 2.200		53.34 2.100		---		71308-5446				71308-5646				71308-6446				71308-6646		46			
				48		60.96 2.400		58.42 2.300		55.88 2.200		---		71308-5448				71308-5648				71308-6448				71308-6648		48			
				50		63.50 2.500		60.96 2.400		58.42 2.300		---		71308-5450		71308-5550		71308-5650				71308-6450		71308-6550		71308-6650		50			
				52		66.04 2.600		63.50 2.500		60.96 2.400		---		71308-5452				71308-5652				71308-6452				71308-6652		52			
				54		68.58 2.700		66.04 2.600		63.50 2.500		---		71308-5454				71308-5654				71308-6454				71308-6654		54			
				56		71.12 2.800		68.58 2.700		66.04 2.600		---		71308-5456				71308-5656				71308-6456				71308-6656		56			
				58		73.66 2.900		71.12 2.800		68.58 2.700		---		71308-5458				71308-5658				71308-6458				71308-6658		58			
				60		76.20 3.000		73.66 2.900		71.12 2.800		---		71308-5460				71308-5660				71308-6460				71308-6660		60			
				62		78.74 3.100		76.20 3.000		73.66 2.900		---		71308-5462				71308-5662				71308-6462				71308-6662		62			
				64		81.28 3.200		78.74 3.100		76.20 3.000		---		71308-5464				71308-5664				71308-6464				71308-6664		64			
				66		83.82 3.300		81.28 3.200		78.74 3.100		---		71308-5466				71308-5666				71308-6466				71308-6666		66			
				68		86.36 3.400		83.82 3.300		81.28 3.200		---		71308-5468				71308-5668				71308-6468				71308-6668		68			
				70		88.90 3.500		86.36 3.400		83.82 3.300		---		71308-5470				71308-5670				71308-6470				71308-6670		70			
				72		91.44 3.600		88.90 3.500		86.36 3.400		---		71308-5472				71308-5672				71308-6472				71308-6672		72			
				74		93.98 3.700		91.44 3.600		88.90 3.500		---		71308-5474				71308-5674				71308-6474				71308-6674		74			
				76		96.52 3.800		93.98 3.700		91.44 3.600		---		71308-5476				71308-5676				71308-6476				71308-6676		76			
				78		99.06 3.900		96.52 3.800		93.98 3.700		---		71308-5478				71308-5678				71308-6478				71308-6678		78			
				80		101.60 4.000		99.06 3.900		96.52 3.800		---		71308-5480				71308-5680				71308-6480				71308-6680		80			
				82		104.14 4.100		101.60 4.000		99.06 3.900		---		71308-5482				71308-5682				71308-6482				71308-6682		82			
				84		106.68 4.200		104.14 4.100		101.60 4.000		---		71308-5484				71308-5684				71308-6484				71308-6684		84			
				86		109.22 4.300		106.68 4.200		104.14 4.100		---		71308-5486				71308-5686				71308-6486				71308-6686		86			
				88		111.76 4.400		109.22 4.300		106.68 4.200		---		71308-5488				71308-5688				71308-6488				71308-6688		88			
				90		114.30 4.500		111.76 4.400		109.22 4.300		---		71308-5490				71308-5690				71308-6490				71308-6690		90			
				92		116.84 4.600		114.30 4.500		111.76 4.400		---		71308-5492				71308-5692				71308-6492				71308-6692		92			
				94		119.38 4.700		116.84 4.600		114.30 4.500		---		71308-5494				71308-5694				71308-6494				71308-6694		94			
				96		121.92 4.800		119.38 4.700		116.84 4.600		---		71308-5496				71308-5696				71308-6496				71308-6696		96			
				98		124.46 4.900		121.92 4.800		119.38 4.700		---		71308-5498				71308-5698				71308-6498				71308-6698		98			
				100		127.00 5.000		124.46 4.900		121.92 4.800		---		71308-5500				71308-5700				71308-6500				71308-6700		100			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[15-91-1588](#)