





REV.	DATE	DESCRIPTION
NC	08/03/98	INITIAL RELEASE
A	01/11/07	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIMS.



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .255"
2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068"

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.						01/11/07
6						CHECKED							
5						ISSUED			PART DESCRIPTION				
4	FERRULE	COPPER	NICKEL	1		DO NOT SCALE DRAWING	SHEET	1 OF 1		TNC REVERSE POLARITY CRIMP PLUG (FOR RG-8X, LMR240 CABLE)			
3	CONTACT PIN	PHOS. BRONZE	GOLD	1					PART NO.				
2	INSULATOR	TEFLON	NATURAL	1					122408RP				
1	BODY	BRASS	NICKEL	1									
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE	C:/122/122408RP.DWG	DWG. NO.	122408RP.DWG	REV. A	SIZE A	SCALE NA	