


## Jacks



### Littel Jax® Phone Jacks

Mate with standard .25" (6.35 mm) or .21" (5.33 mm) phone plugs. Notched insulating washers. Mounts in single .375" (9.52 mm) hole, panels up to .156" (3.96 mm) thick, except Types L-11 and L-12A in panels up to .25" (6.35 mm) thick.

Stock No.	Mfr.'s Type	No. of Conductors	Mating Plug	Description	EACH		
					1-9	10-24	25-99
932-1001	11	2	250	Open circuit	1.52	1.35	1.13
932-0013	C11	2	440, 445, 470	M641/6-1	2.84	2.50	2.11
932-0023	L11	2	250	0.375" lg. bushing	1.84	1.60	1.32
932-1002	12A	2	250	Tip shunt	1.86	1.59	1.35
932-0014	C12A	2	440, 445, 470	M641/12-1	3.79	3.28	2.96
932-0024	L12A	2	250	0.375" lg. bushing	2.23	1.98	1.80
932-0050	13A	2	250	Isolated "make" circuit	4.22	3.69	3.30
932-0051	13A	2	250	Transfer circuit	5.01	4.34	3.64
932-0055	13E	2	250	Isolated "break" circuit	5.17	4.56	3.83
932-0042	12B	3	267	Double open circuit	1.95	1.69	1.40
932-0015	C12B	3	480	M641/5-1	3.58	3.16	2.69
932-0025	L12B	3	267	0.375" lg. bushing	2.07	1.83	1.63
932-0035	S12B	3	480	0.21" i.d. bushing	3.21	2.89	2.42
932-0052	13B	3	267	Tip shunt	5.09	4.41	3.76
932-1003	14B	3	267	Double closed circuit	4.55	3.95	3.59

### Jack Covers

Spring loaded phone jack covers seal jack openings when phone plug is removed. Use with standard 3/8" 32 threaded bushing type phone jacks.

Stock No.	Mfr.'s Type	No. of Conductors	Material	1-9	10-24	25-99
932-1280	512	—	Bright nickel	7.31	6.60	5.98
932-1283	515	—	Black	6.74	5.46	4.64

### Thick-Panel Jax®

Brass, nickel-plated phone jacks with long bushing. Mounts in .469" (11.91 mm) dia. hole in panels up to 1.25" (31.75 mm) thick. Solder lug terminals.


Stock No.	Mfr.'s Type	No. of Conductors	Mating Plug	Description	1-9	10-24	25-99
932-1009	151	2	240, 245, 250	Standard 0.25"	6.57	5.30	4.49
932-1010	152B	3	255, 270, 280 260, 267, 269 297, 260, 267	Standard 0.25"	8.37	7.39	6.71

### Cable Extension Jax®

Standard .25" (6.35 mm) extension phone jacks. Size: .688" (17.48 mm) O.D.; 2.156" (54.76 mm) lg. Types 121 and 131. 5" (12.7 mm) O.D.; 2.5" (63.5 mm) lg. Shielded handles are brass, bright nickel plated. Black handles are plastic.

Stock No.	Mfr.'s Type	No. of Conductors	Mating Plug	Description	1-9	10-24	25-99
932-1006	80	2	240	Screw term., black handle	5.57	4.50	4.39
932-1007	120	2	270	Screw term., shielded	7.12	6.29	5.71
932-1008	121	2	280	Solder term., shielded	6.18	5.35	4.89
932-0065	125	2	740, 745, 750	Solder term., shielded	4.45	3.53	3.05
932-0071	131	3	297	Solder term., shielded	7.51	6.18	5.16
932-0083	830	3	260	Screw term., black handle	7.59	6.24	5.22
932-0123	1238	3	297	Solder term., shielded	8.19	7.37	6.18

## Plugs



### Littel-Plug® Phone Plugs

Fit standard .25" (6.35 mm) extension phone jacks. Solder terminal plugs have built-in cable clamp. Shielded Metal Handles. Nickel-Plated Brass or Durable Molded Plastic: 1.688" (42.88 mm) long x .5" (12.7 mm) dia. Max. Cable Diameter: .297" (7.54 mm).

Stock No.	Mfr.'s Type	No. of Conductors	Handle	Terminals	EACH		
					1-9	10-24	25-99
932-1014	240	2	Black	Screw	3.55	3.14	2.67
932-0945	245	2	Red	Screw	3.56	3.14	2.68
932-1015	250	2	Black	Solder lugs	2.42	2.07	1.89
932-0955	255	2	Red	Solder lugs	3.41	3.00	2.48
932-1018	270	2	Shielded	Screw	5.05	4.45	3.73
932-1019	280	2	Shielded	Solder lugs	3.53	3.12	2.62
932-0950	S250*	2	Black	Solder lugs	3.66	3.14	2.63
932-0980	S280*	2	Shielded	Solder lugs	4.93	4.30	3.84
932-1016	260	3	Black	Screw	5.54	4.90	4.45
932-0960	S260*	3	Black	Screw	7.11	6.40	5.37
932-1017	267	3	Black	Solder lugs	3.53	3.12	2.84
932-0969	269	3	Red	Solder lugs	4.83	4.19	3.77
932-1020	290	3	Shielded	Screw	6.13	5.31	4.83
932-0997	297	3	Shielded	Solder lugs	4.21	3.79	3.17
932-0800	480	3	Black	Solder lugs	11.48	10.44	9.48
932-8600	482	3	Red	Solder lugs	10.47	9.52	8.65
932-8804	482N	3	Red	Solder lugs	10.47	9.52	8.65
932-8806	483	3	Black	Solder lugs	10.47	9.52	8.65
932-8808	483N	3	Black	Solder lugs	10.47	9.52	8.65

### Two Conductor Phone Plugs for Littel Jax® No. 11

Stock No.	Mfr.'s Type	No. of Conductors	Handle	Terminals	1-9	10-24	25-99
932-0040	40	2	Black	Screw	4.57	4.00	3.60
932-0070	70	2	Shielded	Screw	6.03	5.42	4.93
932-0170	170	2	Shielded	Screw	7.16	6.33	5.75

### Three Conductor Phone Plugs for Littel Jax® No. 12B

Stock No.	Mfr.'s Type	No. of Conductors	Handle	Terminals	1-9	10-24	25-99
932-0060	60	3	Black	Solder	5.31	4.65	4.18
932-0191	190A	3	Shielded	Solder	8.35	7.52	6.31

### Hi-D Jax® Enclosed Phone Jacks

Mate with standard .25" (6.35 mm) phone plugs. Molded body protects integral silver-plated springs. Mounts on .625" (15.88 mm) center in single .375" (9.52 mm) hole in panels up to .156" (3.96 mm) thick.

Stock No.	Mfr.'s Type	No. of Conductors	Mating Plug	Description	EACH		
					1-9	10-24	25-99
932-9390	111	2	250	Open circuit	1.75	1.50	1.36
932-9400	N111	2	250	Molded nylon bushing	2.21	1.92	1.60
932-9391	112A	2	250	Closed circuit	1.80	1.56	1.29
932-9392	N112A	2	250	Molded nylon bushing	2.09	1.85	1.68
932-9393	112B	3	267	Double open circuit	1.72	1.49	1.23
932-9394	N112B	3	267	Molded nylon bushing	1.93	1.68	1.43
932-9395	113B	3	267	Single closed circuit	2.66	2.35	1.98
932-9396	N113B	3	267	Molded nylon bushing	3.09	2.73	2.29
932-9397	114B	3	267	Double closed circuit	2.39	2.11	1.77
932-9398	N114B	3	267	Molded nylon bushing	3.21	2.84	2.58

### Tini-Jax® Miniature Phone Jacks

Miniature phone jacks approximately 1/2 the size of Littel-Jax jack, otherwise similar in construction. Mounts in .25" (6.35 mm) dia. hole, panels up to .125" (3.18 mm) thick.

Stock No.	Mfr.'s Type	No. of Conductors	Mating Plug	Description	1-9	10-24	25-99
932-1004	41	2	750	Open circuit	1.33	1.06	.96
932-1005	42A	2	750	Closed circuit	1.93	1.65	1.48

### Micro Jax® Subminiature Phone Jacks

Silver plated, special tempered nickel silver springs. Fits .190" (4.83 mm) dia. hole in panels to .094" (2.39 mm) thick. Only 1/2 the size of standard phone jacks.

Stock No.	Mfr.'s Type	No. of Conductors	Mating Plug	Description	1-9	10-24	25-99
932-9404	TR2A	2	850, 880	Closed circuit	2.19	1.76	1.52

### Right-Angle Miniature Power Jacks

Power jack for PC mounting. Made of heat resistant materials for high temperature soldering. Sleeve/shunt spring functions as a built-in switch. Center Pin: Brass, nickel-plated.

Stock No.	Mfr.'s Type	Pin Dia. (in.)*	Mating Plug	Description	EACH		
					1-9	10-24	25-99
932-9415	RAPC712	0.10	760, 765	Right angle PC terms	1.03	.84	.71
932-9425	RAPC722	0.08	S-760, S-765	Right angle PC terms	.92	.75	.64
932-9430	RASM712	0.10	760, 765	Right angle SM terms	1.13	.99	.90
932-9432	RASM722	0.08	S-760, S-765	Right angle SM terms	1.32	1.16	1.05
932-9434	RASM732	0.05	860, 865	Right angle SM terms	1.76	1.53	1.39

### Miniature Power Jax

Power jacks are 2-cond. type with shunted sleeve. Recessed center pin (712A) .100" (2.54 mm) dia.; (722A) .06" (2.03 mm) dia., split to hold mating plug firmly.

Stock No.	Mfr.'s Type	No. of Conductors	Mating Plug	Description	1-9	10-24	25-99
932-9403	712A	0.10	760, 765	Solder lugs	2.15	1.83	1.67
932-9412	PC712	0.10	760, 765	Straight PC terms	2.14	1.91	1.73
932-9405	722A	0.08	S-760, S-765	Solder lugs	2.15	1.84	1.67
932-9420	PC722A	0.08	S-760, S-765	Straight PC terms	2.67	2.32	2.09

\*Center pin diameter.

### Flat-Plug Phone Plugs

.25" (6.35 mm) phone plugs have flat, space-savings handles.

Stock No.	Mfr.'s Type	No. of Conductors	Handle	Terminals	EACH		
					1-9	10-24	25-99
932-0220	220†	2	Black	Screw	4.27	3.71	3.33
932-0227	227†	2	Black	Solder	2.73	2.36	2.13
932-1013	228†	2	Shielded	Solder	3.91	3.41	3.08
932-1021	226†	2	Shielded	Clamp	3.91	3.38	3.04
932-0230	230†	3	Black	Screw	6.13	5.31	4.83
932-0237	237†	3	Black	Solder	5.49	4.43	3.88
932-0238	238†	3	Shielded	Solder	6.56	5.40	4.58

### Tini-Plug® Miniature Phone Plugs

For use with Tini-Jax jacks. 1/2 size of standard phone plugs. Overall Length: 1.609" (40.87 mm). Handles: plastic or nickel-plated brass. Max. Cable Diameter: .218" (5.54 mm).

Stock No.	Mfr.'s Type	No. of Conductors	Handle	Terminals	1-9	10-24	25-99
932-1022	740	2	Black	Screw	2.62	2.16	1.81
932-0745	745	2	Red	Screw	3.18	2.77	2.48
932-0750	750	2	Black	Solder	2.31	1.84	1.56
932-0755	755	2	Red	Solder	3.00	2.43	2.07
932-0780	780	2	Shielded	Solder	3.49	2.88	2.41

### Micro-Plug® Subminiature Phone Plugs

Only 1.106" (28.81 mm) long; .25" (6.35 mm) O.D., .097" (2.46 mm) diameter sleeve. Screw-on anodized aluminum handles. For cables up to .125" (3.28 mm) diameter. Integral cable clamps mates with TR-2A.

Stock No.	Mfr.'s Type	No. of Conductors	Handle	Terminals	1-9	10-24	25-99
932-1024	850	2	Black	—	2.35	2.06	1.85
932-0855	855	2	Red	—	3.20	2.73	2.45
932-0880	880	2	Natural	—	3.37	2.73	2.45

### Miniature Power Plugs

Mates with sockets used on transistorized portable radios, tape recorders, appliances which have AC adapters, and/or battery chargers. 218" (5.54 mm) O.D. x .375" (9.53 mm) long sleeve. An .062" (1.57 mm) wide insulator. Ring at tip of sleeve insulates and recesses a hollow pin conductor with a center hole of .100" (2.54 mm) I.D.

Stock No.	M
-----------	---