



Wiha Vinyl Grip Pliers & Cutters

Standard Adjustable Pliers



326 Adjustable Pliers - Box Type DIN ISO 5745

10 different opening sizes provide optimal adjustment to objects being gripped. Long durability achieved through additional induction hardening of jaws to approx. 58-60 HRC. Chrome-vanadium tool steel, hardened and tempered. Soft vinyl grips are oil and solvent resistant.

Item				Capacities		
No.		mm	Inch	Round	Hex	Pkg. wt.
326 60	Z21018001	180	7.0	1.25	1 1/2	1 .35
326 61	Z21025001	250	10.0	1.75	2"	1 .67
326 63	Z21030001	300	12.0	2.0	2 1/4	1 1.21

Slide Lock Adjustable Pliers - "QuickFix"



- Open and slide to adjust opening size
- Audible click at each locking position
- Close to lock

326 68 Slide Lock Adjustable Pliers - Wiha QuickFix - Box Type DIN ISO 8976

Super fast and easily adjusted pliers. Long durability achieved through additional induction hardening of jaws to approx. 56 HRC. Finger jam protection for safe operation in all settings. Chrome-vanadium tool steel, hardened and tempered. Soft vinyl grips.

Item				Capacities		
No.		mm	Inch	Round	Hex	Pkg. wt.
326 68	Z23025001	250	10.0	1 1/4	1 1/2	1 .72

Rapid Adjustable - Push Button Pliers



- Fast push button jaw release
- Finger jam protection in all settings

326 Push Button Adjustable Water Pump Pliers - DIN ISO 8976

Extra narrow head for working in restricted spaces. Rapid and simple push button setting and locking. Long durability achieved by additional inductive hardening of gripper jaws to approx. 58-60 HRC. Finger jam protection in all settings ensures safe operation. Chrome-vanadium tool steel, hardened and tempered. Soft vinyl grips. For gripping and holding pipes and angular profiles such as hex nuts in the installation area.

Item				Capacities		
No.		mm	Inch	Round	Hex	Pkg. wt.
326 64	Z22018001	180	7.0	1.25	1 1/2	1 .35
326 65	Z22025001	250	10.0	1.75	2"	1 .67
326 67	Z22030001	300	12.0	2.0	2 1/4	1 1.21



326 69 3 Pc. Push Button Set

Drop-forged from special tool steel, individually high frequency induction hardened. Precision formed. Soft vinyl grips, oil & solvent resistant.

Item# 32669 Set Includes: wt. 2.2

32664 - Push Button Adjustable Water Pump Pliers - 7.0"

32665 - Push Button Adjustable Water Pump Pliers - 10.0"

32667 - Push Button Adjustable Water Pump Pliers - 12.0"

326 70 3 Pc. Adjustable Pliers Set

Drop-forged from special tool steel, individually high frequency induction hardened. Precision formed. Soft vinyl grips, oil & solvent resistant.

Item# 32670 Set Includes: wt. 2.2

32660 - Adjustable Pliers, Box Type - 7.0"

32661 - Adjustable Pliers, Box Type - 10.0"

32663 - Adjustable Pliers, Box Type - 12.0"