





REV.	DATE	DESCRIPTION
A	03/18/05	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.60mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.					03/18/05	
7						CHECKED			PART DESCRIPTION BNC CRIMP JACK (FOR AT&T 734A CABLE - 75ohm)				
6						ISSUED							
5						SHEET	1 OF 1		PART NO. 112973				
4	FERRULE	COPPER	NICKEL	1									
3	CONTACT PIN	PHOS. BRONZE	GOLD	1				DWG. NO. 112973.DWG					
2	INSULATOR	TEFLON	NATURAL	1									
1	BODY	BRASS	NICKEL	1				REV.	A	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY									