



FEATURES:

- Grabber hook attaches to terminals sizes up to .060" (1,5 mm) O.D.
- Hook material is gold plated beryllium copper for superb strength and low contact resistance.
- For added safety, the grabber body material is fire retardant Nylon 6.
- Stainless steel grabber compression spring resists corrosion and retains a firm feel throughout the life of the grabber.
- Flexible 20 gauge multi-stranded wire is molded directly to the grabber actuator cap and pin tip plug for durability.
- Minigator features a maximum jaw opening of 0.187" (4,75 mm) and includes a flexible vinyl boot for insulation protection.

MATERIALS:

Minigrabber® Test Clip: Contact, Beryllium Copper, Gold Plated Spring, Stainless Steel

Insulation: Nylon 6 (Fire Retardant UL94V-0), Matches Wire Color

Wire: 20 AWG, Stranding 41 x 36 copper, PVC Insulated, 0.087" (2,21 mm) O.D.
 Color per part number

Marking: Pomona 4652-XX-*

Insulated Minigator® Test Clip: Body - Steel, Nickel Plated
 Flex Boot - Vinyl, Color Matches Wire Color

RATING:

Operation Temperature: 55°C (+176°F) Max.

Operating Voltage: 30VAC/60VDC Max.

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 4652-XX-*

XX = Length in inches, Standard Lengths: 12" (30,48 cm), 24" (60,96 cm), 36" (91,44 cm) & 48" (121,92 cm)

* = Color, Std. Colors: -0 Black & -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4652-24-2](#)