

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-15-014706	09OCT2015	DL	CW
	B1	ECR-15-016505	11NOV2015	DL	CW
	B2	ECR-16-009730	06JUL2016	BS	CW
	B3	ECR-16-018198	10FEB2017	QY	CW


NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 400 V
RATED CURRENT: 16 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-4.0 mm² (26-12 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20300X10XX000)




注释:

- 技术参数:
绝缘材料: PC
额定电压: 400V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-4.0 mm² (26-12 AWG)
接线类型: 冷压接
- 端子需要单独订购.
(订货号参考图面: T20300X10XX000)

M3 SCREW RECOMMENDED
TIGHTENING TORQUE 0.2Nm
M3螺丝 推荐锁紧力矩0.2Nm




M3 SCREW RECOMMENDED
TIGHTENING TORQUE 0.2Nm
M3螺丝 推荐锁紧力矩0.2Nm





TYPE-1: T2080052101-000 TE LOGO
类 型-1: T2080052101-000 TE LOGO

TYPE-2: T2080052101-001 STAINLESS STEEL SCREW, TE LOGO
类 型-2: T2080052101-001 不锈钢螺丝, TE LOGO








GROUNDING CONTACT TYPE: SCREW CONTACT
GROUNDING CONTACT FINISH: SILVER PLATED
WIRE RANGE: 2.5mm (AWG14)
接地端子类型: 螺丝连接端子 / 接地端子表面处理: 镀银 / 接线范围: 2.5mm² (AWG14)




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 10JAN2015		 TE Connectivity											
		CHK Chris Wang 10JAN2015													
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Xiang Xu 10JAN2015											
		0 PLC ±-		NAME HQ-005-M											
		1 PLC ±-		SIZE A3											
		2 PLC ±-													
		3 PLC ±-													
4 PLC ±-		PRODUCT SPEC 108-137054					CAGE CODE 00779		DRAWING NO T2080052101000		RESTRICTED TO -				
ANGLES ±-		APPLICATION SPEC 114-137054													
MATERIAL - -		FINISH - -		WEIGHT -											
Customer Drawing										SCALE 2:1		SHEET 1 OF 2		REV B3	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




NOTES:
SEE SHEET 1
注释:
见页 1

ALL DIMENSIONS ARE SAME AS TYPE 1,
EXCEPT THOSE DEFINED IN THIS TYPE.
除了在本类型中定义的尺寸外, 其它尺寸同类型 1



TYPE-3: T2080052101-002 STAINLESS STEEL SCREW, NO LOGO
类 型-3: T2080052101-002 不锈钢螺丝, 无LOGO

T2080052101-002	HQ-005-M	HQ-005 MALE INSERT, STAINLESS STEEL SCREW, NO LOGO HQ-005 公插, 不锈钢螺丝, 无LOGO	TYPE-3 类 型-3
T2080052101-001	HQ-005-M	HQ-005 MALE INSERT, STAINLESS STEEL SCREW HQ-005 公插, 不锈钢螺丝	TYPE-2 类 型-2
T2080052101-000	HQ-005-M	HQ-005 MALE INSERT HQ-005 公插	TYPE-1 类 型-1
PART NUMBER 料 号	PART DESCRIPTION 描 述		TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN David Wang 10JAN2015	 TE Connectivity		
		CHK Chris Wang 10JAN2015			
		APVD Xiang Xu 10JAN2015	NAME HQ-005-M		
DIMENSIONS: mm		PRODUCT SPEC 108-137054	SIZE A300779		
		APPLICATION SPEC 114-137054			
MATERIAL -		WEIGHT -	CAGE CODE G-T2080052101000		RESTRICTED TO -
		Customer Drawing	SCALE 2:1	SHEET 2 OF 2	REV B3