

LOC	DIST	REVISIONS				
		F	LTR	DESCRIPTION	DATE	DWN APVD
	22	G		ECO-06-24626	26OCT06	MB MM
		G1		REVISED PER ECO-09-021510	05SEP09	KK AEG

- 1



MATERIAL: HSG-GLOSS REINFORCED FLAME RETARDANT POLYESTER, COLOR-BLACK. CONTACT- BERYLLIUM COPPER FINISH .000030 MIN THK GOLD IN CONTACT AREA WITH .000150 MIN THK TIN-LEAD ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
2. THIS CONNECTOR IS DESIGNED TO ACCOMMODATE A .064±.005 THK PC BOARD.
- 3

THIS CONNECTOR IS DESIGNED TO MOUNT ON RECOMMENDED HOLE PATTERN.
- 4


SELECTIVE LOAD, FIVE CIRCUITS TO BE EMPTY.
- 5

MATERIAL: HSG-GLOSS REINFORCED FLAME RETARDANT POLYESTER, COLOR-BLACK. CONTACT- BERYLLIUM COPPER FINISH .000030 MIN THK GOLD IN CONTACT AREA WITH .000150 MIN THK TIN ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 6

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



VIEW K-K
AMP LOGO LOCATION
SCALE 5:1



RECOMMENDED MOUNTING HOLE PATTERN 3

OBSOLETE	SELECTIVE LOAD 4	.495	.400	7-DUAL SOLDERTAIL	5	5-382200-3
OBSOLETE	-	1.895	1.800	35-DUAL SOLDERTAIL	5	5-382200-2
OBSOLETE	-	.795	.700	13-DUAL SOLDERTAIL	5	5-382200-1
6 OBSOLETE	SELECTIVE LOAD 4	.495	.400	7-DUAL SOLDERTAIL	1	382200-3
6 OBSOLETE	-	1.895	1.800	35-DUAL SOLDERTAIL	1	382200-2
6 OBSOLETE	-	.795	.700	13-DUAL SOLDERTAIL	1	382200-1

REMARKS	B	A	DESCRIPTION	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.				
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN K.SALMEN 5-11-89 CHK A.MILLER 5-11-89 APVD -	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
	0 PLC ± -	PRODUCT SPEC	CONNECTOR ASSY, MINI-EDGE	
	1 PLC ± -	APPLICATION SPEC	-	
MATERIAL 1	2 PLC ± -	SIZE	CAGE CODE	DRAWING NO
	3 PLC ± .010	WEIGHT	-	-
	4 PLC ± -	SCALE	10:1	SHEET 1 OF 1
ANGLES	FINISH 1	CUSTOMER DRAWING	REV	G1