

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0745264070](#)
Status: **Active**
Overview: [lanelink](#)
Description: 0.50mm (.020") Pitch LaneLink™ 10Gbase-CX4 Cable Assembly, 26 AWG, Lanyard Latch, 7.0m (22.97') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	74526
Connector to Connector	4X Plug-to-4X Plug
Overview	lanelink
Product Name	10Gbase-CX4, 4X, LaneLink™

Physical

Cable Length	7.0m (22.97')
Circuits (Loaded)	16
Gender	Plug/Plug
Lock to Mating Part	Yes
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	26
Wire/Cable Type	Round

Electrical

Current - Maximum per Contact	0.5A
Impedance	100#
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-74526-400
---------------	--------------



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[74526Series](#)

Mates With

[91525](#) 4X/12X Latch LaneLink™ Receptacle. [91804](#) LaneLink™ Connector

Use With

[74735](#) X2 Transceiver. [74739](#) XPAK Transceiver