








7. MATERIAL - HOUSING: PLASTIC; GROMMET/SEAL: RUBBER
6. CONTACT FACTORY FOR SAE J1939-15 CONNECTOR USAGE.
5. THIS RECEPTACLE MATES WITH DTM06-2S-**** PLUG.
(**** = ALL MODIFICATIONS)
4. INTERNAL RESISTOR: 110Ω MIN., 120Ω NOM., 130Ω MAX., .4 WATTS MIN..
3. SECONDARY WEDGE LOCK IS INCLUDED WITH RECEPTACLE.
2. DIMENSION TOLERANCE: .025 [.64].
1. ALL DIMENSIONS ARE IN INCHES [mm].

NOTES: UNLESS OTHERWISE SPECIFIED

REV
A

DTM04-2P-EP10

REVISIONS

SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. P17776	5/24/02	RDR
A	REVISED & REDRAWN PER E.O. P20078	12-11-08	RDR

SIGNATURE & DATE	
DR	R. MCCORD 11/19/08
CHK	Paul M. Cal 11/19/08
PE	Paul M. Cal 11/19/08
APPD	D. Mery 11/19/08
SCALE	NONE

RECEPTACLE, 'B' KEY
2 CONTACTS W/ RESISTOR
COLOR: BLACK
EP10 MOD
DTM SERIES
ENVELOPE

EP	MATL CODE
3850 INDUSTRIAL AVE. HEMET, CA 92545	
DEUTSCH INDUSTRIAL	
B	DTM04-2P-EP10
DWG SIZE	CODE 11139 SHEET 1 OF 1