


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0007018101
Status: Active
Description: Commoning Crimp Housing Receptacle Housing, 10 Circuits

Documents:
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	1461
Application	Power
Comments	Circuit are Labeled with Ink Stamped Numbers
Product Name	Commoning Connector
UPC	800753755260
Physical	
Circuits (maximum)	10
Circuits Detail	Circuits Labeled 1-5
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Resin	Polyester
Net Weight	12.625/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	4.45mm
Pitch - Termination Interface	4.45mm
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40°C to +105°C
Electrical	
Current - Maximum per Contact	12.0A
Material Info	
Old Part Number	1461-10E
Reference - Drawing Numbers	
Sales Drawing	SD-1461-*



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per -ED/79/2015 (17 December 2015) Halogen-Free Status Not Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS ELV
	Green Image Not Relevant

Search Parts in this Series
[1461](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[07-01-8101](#) [07-01-7104](#) [07-01-7207](#) [07-01-7107](#) [07-01-7204](#) [07-01-7102](#) [07-01-7152](#) [07-01-7103](#) [07-01-7157](#)
[07-01-7057](#) [07-01-7153](#) [07-01-7154](#) [07-01-7202](#) [07-01-7203](#)