


REV.	DATE	DESCRIPTION
NC	04/11/02	INITIAL RELEASE
A	12/11/07	REVISE CONTACT PIN MATERIAL / UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
8	MOUNTING POST	BRASS	BRT. TIN	1		DRAWN	G.R.S.						12/11/07
7	POST	COPPER	BRT. TIN	1		CHECKED							
6	POST	COPPER	BRT. TIN	1					PART DESCRIPTION DUAL PORT BNC R/A PCB MOUNT RECEPTACLE – BLACK 50ohm				
5	HOUSING	PBT	RED	1		ISSUED							
4	CONTACT PIN	PHOS. BRONZE	BRT. TIN	1		SHEET	1 OF 1		PART NO. 112705				
3	CONTACT PIN	PHOS. BRONZE	BRT. TIN	1									
2	INSULATOR	POLY PRO	NATURAL	1				DWG. NO. 112705.DWG REV. A SIZE A SCALE NA					
1	BODY	ZINC DIE CAST	NICKEL	1									
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE C:/112/112705.DWG							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112705](#)