


Sales Outline DrawingRevision **A****Specifications:**

Sound level Category	Soft Sound Level
Mode of Operation	Continuous
Mounting	Panel (see note A)
Voltage Rating	4 - 28 Vdc
Frequency	2900 Hz 500 Hz
Loudness (Min. Voltage)	52 dB(A) min. @ 2 FT and 4 Vdc
Loudness (Max Voltage)	68 dB(A) min. @ 2FT and 28 Vdc
Current Draw	0.5 mA Max @ 4 Vdc
Current Draw	3 mA Max @ 28 Vdc
Storage Temperature	-40°C to +85°C
Operating Temperature	-30°C to +65°C
Weight (Typical)	0.5 oz (17 g)
Housing	6/6 Nylon, Color Black
Options	For other options contact factory

Dimensions: Inches (mm)**RoHS Compliant**

NOTE A:

MOUNTING - THIS PORTION
SNAP-LOCKS INTO PANELS 1/32" TO
1/8" THICK USING APPROPRIATE
COMPRESSION WASHER.
1.063 ±.005 DIA. PANEL HOLE REQ'D.



NOTE B:

TERMINALS - .016 BRASS, HOT TIN FINISH WITH
.076 WIRE HOLE. TERMINAL WILL ACCEPT
STANDARD 1/8" QUICK CONNECT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[SNP428FR](#)