


DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION




© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

MOD 20 LOC BD DIST 39

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
			0	RELEASED	
			0	REVISED ECN-0048	4-10-84
			A	REV PER ECN BD2622	3-18-85
			B	REV PER ECN BD4356	08/28/85



- CONNECTORS COMPLY WITH AMP SPEC. 108-40,012 AND MATE WITH ANY SAME NUMBER POSITION RECEPTACLE CONNECTOR IN AMPLIMITE SERIES.
 - CONNECTOR DESIGNED FOR 28 AND 26 AWG STRANDED AND SOLID CONDUCTOR RIBBON CABLE ON .050.
- △ DIMENSION APPLIES TO TERMINATED CONNECTOR.
△ MOLDED PARTS, FLAME RETARDANT 94V-0 RATED THERMOPLASTIC, COLOR: BLACK.
△ PHOS. BRONZE PER QQ-B-750.
△ GOLD PLATING PER MIL-G-45204, BRIGHT TIN PLATING PER MIL-T-10727 (NOT TIN LEAD), NICKEL PLATING PER QQ-N-290.
△ .000030 GOLD ON MATING END, .000100-.000200 BRIGHT TIN OR BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
△ DIMENSION APPLIES TO BASE OF SHROUD.



1.216	.984	.759	.666	.400	8	9	747321-4
1.541	1.312	1.087	.994	.700	14	15	747321-3
2.090	1.852	1.623	1.534	1.200	24	25	747321-2
2.732	2.500	2.275	2.183	1.800	36	37	747321-1
F	E	D	C	B	A	NO. OF POS.	PART NUMBER

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.
TOLERANCES ON:
DECIMALS $\pm .005$
ANGLES $\pm 2^\circ$

MATERIAL
MOLDED PARTS: △
CONTACTS: △

FINISH △
CONTACTS: △

CONTRACT NO

DR J. GERACE 9-16-83

CHK J. GERACE 9-16-83

APPD D. HOFFMAN 10-3-83

APPD T. LYZINSKI 10-4-83

OSGN APPD

OTHER APPD

AMP AMP INCORPORATED
Harrisburg, Pa.NAME
PLUG ASSEMBLY, LOW PROFILE HDF,
W/ PREASSEMBLED COVER

SIZE FSCH NO DRAWING NO

C

00779

747321

SCALE

SHEET 1 OF 1

CUSTOMER DRAWING