

LABELS THAT STICK  
 & STAY STUCK

RHINO labels are as exceptional as the RHINO 6000. Easy to use and super-strong, they're designed for the long haul. Thanks to industrial-strength adhesives, they deliver the lasting durability and legibility you demand – in six materials, for a multitude of applications. To meet your high standards, RHINO labels are designed to work exclusively with our printers and perform on any surface you encounter.

- Easy-to-peel, split-back styles will speed you along.
- Industrial-strength adhesives help these labels stick and stay stuck – in harsh worksite conditions.
- Thermal transfer print technology produces labels that are durable, smear-proof and resistant to chemicals, solvents, heat, UV and more.



NEW! RHINO self-laminating labels protect your printed area from exposure (to oil, solvents, water and abrasion). Ideal for wire and cable identification, these versatile labels offer excellent conformity to round, irregular and flexible surfaces:

- Specially-formulated to stick and last – on wire and cable
- Resistant to abrasion, chemicals and moisture
- Die-cut labels allow easy “peel away” from liner



**Master Carton:** 3 Units  
 Weight: 12 lbs. (5443.1 grams)  
 Dimensions: 12" H x 12" W x 11" D  
 304.8mm x 304.8mm x 279.4mm (HxWxD)

**RHINO 6000 Professional Labeling Tool**  
 Part No. 1734519    UPC: 0 71701 12173  
*Includes:*  
 RHINO 6000 Printer  
 1" Black on White Flexible Nylon Label Cartridge  
 Li-ion Rechargeable Battery Pack  
 AC Adapter  
 Quick Reference Guide  
 Registration Card  
 Printer Weight: 1.98 lbs. (898.1 grams)  
 Printer Dimensions: 9.7" H x 4.9" W x 2.6" D  
 (245.1mm x 124.9mm x 65.0mm)



**Master Carton:** 3 Units  
 Weight: 24 lbs. (10886.2 grams)  
 Dimensions: 19" H x 14.2" W x 13" D  
 482.6mm x 360.7mm x 330.2mm (HxWxD)

**RHINO 6000 Hard Case Kit**  
 Part No. 1734520    UPC: 0 71701 12174  
*Includes:*  
 RHINO 6000 Printer  
 RHINO CONNECT Software  
 Durable, hard carry case  
 1" Black on White Flexible Nylon Label Cartridge  
 3/8" Black on White Vinyl Label Cartridge  
 Li-ion Rechargeable Battery Pack  
 AC Adapter  
 Quick Reference Guide  
 Registration Card  
 USB Cable  
 Weight: 5.4 lbs. (2449.4 grams)  
 Printer Dimensions: 14" H x 18" W x 4" D  
 (355.6mm x 457.2mm x 101.6mm)

DYMO®

RHINO LABELS

**FLEXIBLE NYLON** – Curved or flat surfaces. Wires, patch panels, machinery, equipment, bins, etc.

| PART #             | DESCRIPTION                            | LENGTH |
|--------------------|----------------------------------------|--------|
| 18488              | White Flexible Nylon Tape 1/2" (12mm)  | 11.5'  |
| 18489              | White Flexible Nylon Tape 3/4" (19mm)  | 11.5'  |
| <b>NEW</b> 1734524 | White Flexile Nylon Tape 1" (24mm)     | 11.5'  |
| 18490              | Yellow Flexible Nylon Tape 1/2" (12mm) | 11.5'  |
| 18491              | Yellow Flexible Nylon Tape 3/4" (19mm) | 11.5'  |
| <b>NEW</b> 1734525 | Yellow Flexible Nylon Tape 1" (24mm)   | 11.5'  |

**PERMANENT POLYESTER** – Flat surfaces. Equipment, bins, patch panels, etc.

| PART #             | DESCRIPTION                           | LENGTH |
|--------------------|---------------------------------------|--------|
| 18482              | White Perm Poly Tape 3/8" (9mm)       | 18'    |
| 18483              | White Perm Poly Tape 1/2" (12mm)      | 18'    |
| 18484              | White Perm Poly Tape 3/4" (19mm)      | 18'    |
| <b>NEW</b> 1734523 | White Perm Poly Tape 1" (24mm)        | 18'    |
| 18508              | Clear Perm Poly Tape 3/8" (9mm)       | 18'    |
| 622289             | Clear Perm Poly Tape 1/2" (12mm)      | 18'    |
| 622290             | Clear Perm Poly Tape 3/4" (19mm)      | 18'    |
| 18485              | Metallized Perm Poly Tape 3/8" (9mm)  | 18'    |
| 18486              | Metallized Perm Poly Tape 1/2" (12mm) | 18'    |
| 18487              | Metallized Perm Poly Tape 3/4" (19mm) | 18'    |

**VINYL** – All surfaces. Ideal for outdoor and color-coding applications. Warning messages, wires, patch panels, equipment, machinery, etc.

| PART # | DESCRIPTION              | LENGTH |
|--------|--------------------------|--------|
| 18443  | White Vinyl 3/8" (9mm)   | 18'    |
| 18444  | White Vinyl 1/2" (12mm)  | 18'    |
| 18445  | White Vinyl 3/4" (19mm)  | 18'    |
| 18431  | Yellow Vinyl 3/8" (9mm)  | 18'    |
| 18432  | Yellow Vinyl 1/2" (12mm) | 18'    |
| 18433  | Yellow Vinyl 3/4" (19mm) | 18'    |
| 18434  | Orange Vinyl 3/8" (9mm)  | 18'    |
| 18435  | Orange Vinyl 1/2" (12mm) | 18'    |
| 18436  | Orange Vinyl 3/4" (19mm) | 18'    |
| 18437  | Red Vinyl 3/8" (9mm)     | 18'    |
| 18438  | Red Vinyl 1/2" (12mm)    | 18'    |
| 18439  | Red Vinyl 3/4" (19mm)    | 18'    |
| 18440  | Green Vinyl 3/8" (9mm)   | 18'    |
| 18441  | Green Vinyl 1/2" (12mm)  | 18'    |
| 18442  | Green Vinyl 3/4" (19mm)  | 18'    |

**HEAT SHRINK TUBE** – Wire and cable.

| PART # | DESCRIPTION                         | LENGTH |
|--------|-------------------------------------|--------|
| 18051  | White Heat Shrink Tube 1/4" (6mm)   | 5'     |
| 18053  | White Heat Shrink Tube 3/8" (9mm)   | 5'     |
| 18055  | White Heat Shrink Tube 1/2" (12mm)  | 5'     |
| 18057  | White Heat Shrink Tube 3/4" (19mm)  | 5'     |
| 18052  | Yellow Heat Shrink Tube 1/4" (6mm)  | 5'     |
| 18054  | Yellow Heat Shrink Tube 3/8" (9mm)  | 5'     |
| 18056  | Yellow Heat Shrink Tube 1/2" (12mm) | 5'     |
| 18058  | Yellow Heat Shrink Tube 3/4" (19mm) | 5'     |

**NON-ADHESIVE** – Patch panels, distribution blocks, faceplates, etc.

| PART # | DESCRIPTION                         | LENGTH |
|--------|-------------------------------------|--------|
| 18111  | White Non-Adhesive Tag 1/4" (6mm)   | 18'    |
| 18112  | White Non-Adhesive Tag 3/8" (9mm)   | 18'    |
| 18113  | White Non-Adhesive Tag 1/2" (12mm)  | 18'    |
| 18114  | White Non-Adhesive Tag 3/4" (19mm)  | 18'    |
| 18115  | Yellow Non-Adhesive Tag 1/4" (6mm)  | 18'    |
| 18116  | Yellow Non-Adhesive Tag 3/8" (9mm)  | 18'    |
| 18117  | Yellow Non-Adhesive Tag 1/2" (12mm) | 18'    |
| 18118  | Yellow Non-Adhesive Tag 3/4" (19mm) | 18'    |

**SELF-LAMINATING** – Protects vital information in harsh environments.

| PART #             | DESCRIPTION                     | LENGTH |
|--------------------|---------------------------------|--------|
| <b>NEW</b> 1734821 | White Self-Laminating 1" (24mm) | 18'    |

RHINO  
 PROFESSIONAL LABELING TOOLS  
 HOW DO YOU SIGN YOUR WORK?™

RHINO 6000  
 PROFESSIONAL LABELING TOOL

Perfect for:

- Datacomm
- Electrical
- Facility Maintenance
- Professional A/V
- Security



PC CONNECTIVITY



Create labels on a PC and download to RHINO 6000, or create and print labels at the worksite. Either way, rugged RHINO 6000 simplifies labeling with advanced functions that are genuine time-savers. And RHINO labels stay stuck, long after you're gone.

- PC connectivity for fast label downloads – and uploads for documentation purposes.
- “Hot Keys” for instant wire and cable wraps, flags, vertical and fixed length labels, patch panels, distribution modules and more.
- Over 250 easy-to-find, pre-programmed industry terms and symbols save you time.
- Save over 1,000 custom labels, including industry terms, graphics, logos and symbols, for on-demand printing at the worksite.
- Large graphic display with backlight for previewing entire label files and increased visibility.
- One-touch powered cutter and cassette ejection system for effortless labels.
- Prints on industrial-strength RHINO labels, NOW up to 1" wide.

RHINO  
 PROFESSIONAL LABELING TOOLS  
 HOW DO YOU SIGN YOUR WORK?™

# RHINO 6000

## PROFESSIONAL LABELING TOOL

If you've "held out" for the best labeling tool with PC Connectivity, feast your eyes (and rest your fingers) on RHINO 6000. Installers tell us the three things they want from a labeling tool are "EASY, EASY and EASY." So go ahead – load and unload label cassettes without hesitation. Use the generously-sized LCD to create, edit and preview multiple labels without breaking a sweat. If you do, our labels resist solvents, UV, moisture, harsh temperatures and, yes, even smearing. For high-end installations and the highest level of satisfaction, RHINO 6000 is built for the long haul – and to please you every step of the way.

**Intuitive Graphical Interface**  
Create, edit and preview multiple labels on our largest backlit LCD


**One-Touch, Power-Assisted Cutter**  
Eliminate the fatigue of manual cutting and increase efficiency

**Hot Keys**  
Eliminate guesswork, complicated menus and enjoy fast and easy formatting of commonly-used label types

**Quick-Charge Li-Ion Rechargeable Battery**  
With on-screen battery life indicator

**Symbols**  
Over 100 pre-programmed industry symbols

**Save Your Labels**  
Customize over 1,000 labels with logos and symbols – and recall them instantly



# FAST



PC CONNECTIVITY

**Library**  
Over 150 pre-programmed industry terms and the ability to customize your own library of terms

**Integrated Impact Bumpers**  
Protects against harsh conditions while allowing easy access to label cartridge

### PC CONNECTIVITY

- Free Windows® driver available at [www.rhinolabeling.com](http://www.rhinolabeling.com) for printing from any Windows® program via USB interface.
- Upgrade printer firmware when new features become available.
- Works best with Rhino CONNECT™ Software\* (not included) to:
  - Upload / download label files for in-the-field and on-demand printing.
  - Insert customized graphics, logos, symbols and industry terms.
  - Import data from any Windows® based program.
  - Create labels using the integrated step-by-step wizard.
  - Print labels directly from RHINO CONNECT™ Software.

**Powerful Serialization**  
Built-in wizards for simple and advanced serialization

# DURABLE

# EASY