

# Saws & Blades

Saws and blades from Klein are designed with the professional user in mind, providing superior results with less effort.



For Professionals...  
Since 1857™

## Saws & Blades

### High-Tension Hacksaw

- Adjustable blade tension up to 30,000 PSI for fast, precise cuts
- Soft-touch grips
- Alternative 45° mounting for flush cutting
- Front mount for reciprocating saw blades
- Blade storage in handle
- Includes 12" x 24 TPI bi-metal hack saw blade and 6" x 24 TPI bi-metal reciprocating saw blade



702-12

| Cat. No. | Blade Length   | Overall Length     | Weight             |
|----------|----------------|--------------------|--------------------|
| 702-12   | 12" (304.8 mm) | 16-1/4" (412.8 mm) | 1.5 lbs. (0.68 kg) |

### Dual-Purpose Hacksaw - Golden Tri-Cut™ 3-in-1 Blade

- Blade has three teeth sizes
- Blade converts quickly to 90° or 45° for standard or flush-cut applications
- Pivot-lock adjusts blade tension for straighter cuts and longer blade life
- Set screw allows for storage of extra blades and secures blade for "jab" sawing
- Aluminum finger grip handle and front end
- Thumb guard for two-hand sawing



701-S

| Cat. No. | Blade Length   | Overall Length | Weight             |
|----------|----------------|----------------|--------------------|
| 701-S    | 12" (304.8 mm) | 16" (406.4 mm) | 1.5 lbs. (0.68 kg) |



Blade has three teeth sizes

### Bi-Metal Blades



1224BI

- Special high-speed steel teeth fused to regular carbon-steel body, which provides superior cutting and longer life
- Withstands greater saw tension for less blade flexing
- Fits all 12" (305 mm) hacksaw blades
- Blue finish
- Available in box of 100 blades or in a reclosable, heavy-vinyl, seal-tight pouch of 10 blades

| Cat. No. | Teeth Per Inch | Overall Length | Package Quantity | Weight             |
|----------|----------------|----------------|------------------|--------------------|
| 1218BI-P | 18             | 12" (304.8 mm) | 10-Pack          | 7.2 oz. (204 g)    |
| 1224BI-P | 24             | 12" (304.8 mm) | 10-Pack          | 7.2 oz. (204 g)    |
| 1232BI-P | 32             | 12" (304.8 mm) | 10-Pack          | 7.2 oz. (204 g)    |
| 1218BI   | 18             | 12" (304.8 mm) | 100-Pack         | 4.5 lbs. (2.04 kg) |
| 1224BI   | 24             | 12" (304.8 mm) | 100-Pack         | 4.5 lbs. (2.04 kg) |
| 1232BI   | 32             | 12" (304.8 mm) | 100-Pack         | 4.5 lbs. (2.04 kg) |

### Golden Tri-Cut™ Blades




1200BI



Blade has three teeth sizes

- Unique design provides three teeth sizes on one blade
- Has 32 teeth/inch up front for quick starts, 24 teeth/inch in the middle and 18 teeth/inch on the end for fast and smooth conventional cutting
- Special high-speed steel teeth fused to carbon-steel provide superior cutting action and long life
- Gold finish
- Available in box of 100 blades or in a reclosable, heavy-vinyl, seal-tight pouch of 10 blades

| Cat. No. | Teeth Per Inch | Overall Length | Package Quantity | Weight             |
|----------|----------------|----------------|------------------|--------------------|
| 1200BI-P | 32-24-18       | 12" (304.8 mm) | 10-Pack          | 7.2 oz. (204 g)    |
| 1200BI   | 32-24-18       | 12" (304.8 mm) | 100-Pack         | 4.5 lbs. (2.04 kg) |



## Saws & Blades

### Jab Saw

- Cuts drywall, wallboard, plywood and plastic
- Triple ground teeth for a fast cut
- Blade cuts in both directions (push and pull)
- Hardened, carbon-steel blade for durability
- Hardened, beveled blade point for scoring and plunge cuts
- Comfort cushion grip with thumb groove
- Handle structure designed for strength and durability
- Flat-end grip for palming or punching through drywall



725

| Cat. No. | Blade Length  | Overall Length | Weight          |
|----------|---------------|----------------|-----------------|
| 725      | 6" (152.4 mm) | 12" (304.8 mm) | 5.0 oz. (142 g) |

### Magic-Slot Compass Saws

- Magic-Slot design allows fast blade changing without removing thumbscrew
- Strong, lightweight, die-cast zinc handle with blue finish is contoured for comfort
- Cat. No. 703 comes with Cat. No. 706 8" blade
- Blade is tough, high-quality carbon steel, 8" (203 mm) long, with ten teeth per inch for general-purpose use
- Cat. No. 702 can be used with Magic-Slot cut-in or general-purpose blades only
- Replacement blades and handle can be ordered separately



703

| Cat. No. | Description                          | Teeth Per Inch | Overall Length | Weight             |
|----------|--------------------------------------|----------------|----------------|--------------------|
| 703      | Magic-Slot Compass Saw with 8" Blade | 10             | 13" (330.2 mm) | 1.2 lbs. (0.54 kg) |
| 702      | Magic-Slot Compass Saw Handle        | —              | 5" (127.0 mm)  | 1.1 lbs. (0.50 kg) |

### Compass Saw Replacement Blades

- For cutting through wallboard or Masonite to install wiring, outlet boxes, etc.
- Tough high-quality carbon steel
- Pointed starter tip
- Fits Magic-Slot compass saw handle Cat. No. 702



709

| Cat. No. | Teeth Per Inch | Overall Length | Weight             |
|----------|----------------|----------------|--------------------|
| 704      | 8              | 12" (304.8 mm) | 2.2 oz. (62 g)     |
| 705      | 10             | 12" (304.8 mm) | 2.2 oz. (62 g)     |
| 706      | 10             | 8" (203.2 mm)  | 1.4 lbs. (0.64 kg) |
| 707      | 10             | 10" (254.0 mm) | 1.9 oz. (54 g)     |
| 709      | 10             | 4" (101.6 mm)  | 1.0 oz. (28 g)     |

### Reciprocating Saw Blades

- Bi-metal blades for different cutting applications of steel and wood
- Shock resistant teeth resist stripping
- 1/2" universal shank to fit all popular reciprocating saw tools

**NOTE:** Read and follow safety instructions in power tool owner's manual.



31716



31728

| Cat. No. | Teeth Per Inch | Blade Length  | Blade Width    | Blade Thickness  | Application        | Package Quantity | Weight          |
|----------|----------------|---------------|----------------|------------------|--------------------|------------------|-----------------|
| 31716    | 6              | 6" (152.4 mm) | 3/4" (19.1 mm) | 0.050" (1.27 mm) | Wood with Nails    | 5-Pack           | 3.6 oz. (102 g) |
| 31728    | 18             | 6" (152.4 mm) | 3/4" (19.1 mm) | 0.035" (0.89 mm) | Heavy Gauge Metals | 5-Pack           | 6.5 oz. (184 g) |
| 31734    | 24             | 6" (152.4 mm) | 3/4" (19.1 mm) | 0.035" (0.89 mm) | 18 Gauge and Under | 5-Pack           | 1.6 oz. (45 g)  |

