

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300250237](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Mini-Change Single-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 16 and 20 AWG, DeviceNet Mid Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Cordsets
Series [130025](#)
Connector End A Mini-Change
Connector End B Mini-Change
IP Rating IP67
Material - Contact Brass
Overview [Brad Mini-Change Connectors](#)
Product Name DeviceNet Trunk, Mini-Change
Region Europe
Type Double Ended
UPC 78678832704

Physical

Cable Diameter 8.38mm (.330")
Cable Length 5.0m (16.40')
Color - Cable Jacket Gray
Coupling Style Threaded
Gender Female-Male
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Coupling Nut Die-Cast Zinc
Material - Plating Mating Gold
Orientation Straight to Straight
Poles 5
Temperature Range - Operating -20°C to +80°C
Wire Size AWG 16, 20
Wire/Cable Type Mid Cable

Electrical


Current - Maximum per Contact 4.0A
Voltage - Maximum 300V AC/DC

Material Info

Engineering Number DNB11A-M050

Reference - Drawing Numbers

Sales Drawing SD-130025-009



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130025](#) Series