

wrenches

467S - 467F - 467



467F
PRODUCTIVITY

ULTRA-MANOEUVRABLE

- Resolves the problems of tightening in situations where the operator must work "blind".
- The articulated ratchet head provides unequalled accessibility, as it is more compact than the traditional ratchet wrench-universal joint-sock combination.



467
PRODUCTIVITY

VERY VERSATILE

- Ring head: 5° ratchet mechanism, angled at 15°.
- Open end angled at 15° for side access.

467.J7PB
3148518296281



7-piece ratchet combination wrench set

7 wrenches: 8-10-12-13-14-17-19 mm.



467S.JP6PB
3148518240345

6-piece set of short ratchet combination wrenches on clip holder

6 wrenches: 8-10-11-12-13-14 mm.



467F.JP10PB
3148518296106

Hinged wrenches

10-piece ratchet combination wrench clip set

10 wrenches: 8-10-11-12-13-14-16-17-18-19 mm.



467.JP10PB
3148518296014



MOD467J12PB
3148518297677

12-piece large ratchet combination wrench module

21-22-24-27-30-32 mm.

12-piece hinged ratchet combination wrench module

Module designed for awkward environments.

- 8-9-10-11-12-13-14-15-16-17-18-19 mm
- + adaptors for sockets (1/4", 1/2") and bits (1/4")

The adaptors transform the wrench into an ultra-compact ratchet for sockets and bits.



MOD.467FJ12PB
3148518297752



MOD.467XLPB
3148518297837

