

Double Row Terminal Blocks

672 RZ Series

600 Volts AC/DC (Classes B/C)



672 RZ 06

Specifications:

- Base, Thermoplastic, 125°C (UL RTI)
- Closed Back Design
- Screws, #8-32 Binder Head, Phil-Slot, Steel
- Terminals, Plated Brass
- 1-24 Poles
- 9/16" Centers
- Wire Range With Wire Binding Screw
#10 - #14 AWG – 30 Amps

- Wire Range With Sems Pressure Screw #10 - #22 AWG
Stranded Copper Wire Only, 30 Amps
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

MSP Catalog #	# of poles	Dimensions	
		A	B
672 RZ 01	1	1.54	1.13
672 RZ 02	2	2.10	1.69
672 RZ 03	3	2.66	2.25
672 RZ 04	4	3.22	2.81
672 RZ 05	5	3.79	3.38
672 RZ 06	6	4.35	3.94
672 RZ 07	7	4.91	4.50
672 RZ 08	8	5.47	5.06
672 RZ 09	9	6.04	5.63
672 RZ 10	10	6.60	6.19
672 RZ 11	11	7.16	6.75
672 RZ 12	12	7.72	7.31
672 RZ 13	13	8.29	7.88
672 RZ 14	14	8.85	8.44
672 RZ 15	15	9.41	9.00
672 RZ 16	16	9.97	9.56
672 RZ 17	17	10.54	10.13
672 RZ 18	18	11.10	10.69
672 RZ 19	19	11.66	11.25
672 RZ 20	20	12.22	11.81
672 RZ 21	21	12.79	12.38
672 RZ 22	22	13.35	12.94
672 RZ 23	23	13.91	13.50
672 RZ 24	24	14.47	14.06

mm=dim X 25.4

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html

Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

CATALOG # MSP	KULKA	PRODUCT DESCRIPTION	PAGE REFERENCE
	KT55	Full Quick Connect (0° Flat)	See page 105
	KT56	Full Quick Connect (45° Bend)	See page 105
	KT57	Full Quick Connect (90° Bend)	See page 105
	KT61	Half Quick Connect (0° Flat)	See page 105
	KT62	Half Quick Connect (45° Bend)	See page 105
	KT63	Half Quick Connect (90° Bend)	See page 105
	ST	Full Solder	See page 106
	3/4 ST	Half Solder	See page 106
	J 602	Line to Line Jumper	See page 107
	3786	SEMS Pressure Saddle Screw	See page 107
	3787	Sems Pressure Saddle Screw with External Tooth Lock Washer	Consult C/S
PSB		Phil-Slot Brass Screw	Consult C/S

Quick Connects: .032" x .250"

See pages 104-115 for terminal block accessories

