





CATALOG LISTING
424EN33-RB
PAGE 1 OF 1


ISSUE
6

REVISIONS

RASTER
DRAWN



- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805, SYMBOL 4
 - 3 - IN ADDITION TO STANDARD MARKING, CUSTOMER PART NUMBER AND CURRENT CUSTOMER DRAWING REVISION LEVEL IS MARKED ON THE SWITCH NAME PLATE IF APPLICABLE
 - 4 - COINCIDENCE OF OPERATION AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - 5 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
 - 6 - GOLD PLATED SILVER CONTACT BASIC SWITCHES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH				THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA			SCALE NONE
OPERATING FORCE — — — — 6-12 LB		CONTACT ARRANGEMENT 4X S P D T			DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE --- 30 LB MAX					
RELEASE FORCE — — — — 4 LB MIN		LOAD	28 VDC		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
PRETRAVEL — — — — .040 MAX			SEA LEVEL	50,000 FT	
DIFFERENTIAL TRAVEL — — .020 MAX		RES	7	ONE PLACE (.0) ±.030	
OVERTRAVEL — — — — .250 MIN		IND	4	TWO PLACE (.00) ±.015	
		MOTOR	4	THREE PLACE (.000) ±.005	
				ANGLES ±	
				WEIGHT	

ANSI Y14.5M-1982 APPLIES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[424EN33-RB](#)