



# DIN Receptacles


16PJ102-E, 16PJ224-E

**KOBI CONN**


DIN Receptacles




3 Pin



16PJ102-E



6 Pin



16PJ224-E

Dimensions: In.

Mouser Stock No.	Description	Degree of Arc
16PJ102-E	3 Pin	180°
16PJ224-E	6 Pin	240°

SPECIFICATIONS	
Rated Power:	2A/34VDC
Contact Resistance:	20mΩ max.
Insulation Resistance:	300MΩ min. @ 500VDC
Dielectric Strength:	1000VAC for 1 Minute
Case:	Nickel Plated Steel
Insulator:	Phenolic
Pin:	Tin Plated Brass
Ground Lug:	Tin Plated Phosphor Bronze
Rivet:	Aluminum
RoHS Compliant	

Date Last Revised: 12-23-05

Available from Mouser Electronics  
1-800-346-6873  
[www.mouser.com](http://www.mouser.com)

KC-300941

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

16PJ102-E 16PJ224-E