

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35189-0281](#)
Status: **Active**
Description: 4.75mm Tab, MP-Lock™ Housing, 2 Circuits, 10.00mm Pitch, UL94V-0, Natural

Documents:

[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-35189-004 \(PDF\)](#)
[Packaging Specification PK-35189-002 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR95446
UL E29179

General

Product Family Crimp Housings
Series [35189](#)
Application Power
Product Name MP-Lock™
UPC 800756383248

Physical

Breakaway No
Circuits (maximum) 2
Flammability 94V-2
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part None
Net Weight 1.333/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 10.00mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40°C to +105°C

Electrical

Current - Maximum per Contact 12A

Material Info

Reference - Drawing Numbers

[Packaging Specification](#) PK-35189-002
[Product Specification](#) PS-35189-004, RPS-35189-002
[Sales Drawing](#) SD-35189-*281




image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[35189Series](#)

Mates With

Appliance Heater

Use With

[35068](#) MP-Lock™ Quick Disconnect

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35189-0281](#)