

[Home](#)[Products](#)[Search](#)[Support](#)[About Us](#)
[Search Engine](#) > Catalog: **DST9NC52A222Q55B**

Noise Suppression Products/EMI Suppression Filters > Lead EMIFIL Capacitor Type > Broad Band Type

PDF Download

'Data Sheet' contains Dimensions, Rated Value and Packaging.

Specification

Global Part Number	DST9NC52A222Q55B
Previous Part Number	DST310-55Y5S222M100
Capacitance	2200pF
Lower Tolerance	-20%
Upper Tolerance	20%
Rated Current	7A
Rated Voltage	100Vdc
Insulation Resistance (min.)	
Withstand Voltage	250Vdc
Max. of DC resistance	
Min. of Operating Temp.	-25°C
Max. of Operating Temp.	+85°C
Length	9.5mm
Width	4.0mm
Thickness	15.5mm
Number of Circuit	1
Case Size	
Weight (Typ.)	1.09g

Details

-  [Part Numbering](#)
-  [Appearance](#)
-  [Dimension](#)
-  [Insertion Loss\(Typ.\)](#)
-  [IL of Main Items](#)
-  [Features](#)
-  [Equivalent circuit](#)
-  [Notice\(Soldring and Mounting\)](#)
-  [Packaging](#)
-  [Notice \(storage and operating condition\)](#)
-  [Caution \(rating\)](#)

Minimum Quantity

180mm Paper Tape	
180mm Plastic Tape	
330mm Paper Tape	
330mm Plastic Tape	
Bulk Case	
Bulk(Bag)	200
Ammo Pack	

320Reel	☐
Magazine	☐
Box	☐

**Product specifications in this catalog are as of September 2005,
and are subject to change or obsolescence without notice.
Please approve our product specifications or transact the approval sheet before ordering.
Please read rating and !Cautions first.**

UP 

| [Site Map](#) | [History](#) | [Terms of use](#) | [Privacy Policy](#) |

All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd. 2005