


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
A	REV. DCN 32243	11/29/04	STW
B	REV. DCN 35434	10/05/07	STW




MATERIALS;
BODY, CONTACT,
EMI-RING, CAP &
ANTI-ROCK RING: BERYLLIUM COPPER PER ASTM B196
INSULATOR: PTFE PER ASTM D1710

FINISHES:
BODY, CONTACT,
EMI-RING, CAP &
ANTI-ROCK RING: GOLD PER ASTM B488, TYPE II
GRADE C, CLASS 1.27, OVER NICKEL
PER AMS-QQ-N-290, CLASS 1

ELECTRICAL:
IMPEDANCE: 50 OHMS
FREQ. RANGE: DC TO 26.5 GHZ
D.W.V.: 500 VOLTS DC
INSULATION RES.: 5,000 MEGOHMS MINIMUM

REF. DSCC 94008ZCG-3

DIMENSIONS ARE IN INCHES WITH METRIC EQUIVALENTS IN BRACKETS [].

MATERIAL: SEE NOTES		DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X"X' ±15' DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE AFTER PLATING. 2) BREAK CORNERS & EDGES .005 R. MAX. 3) CHAM. 1ST & LAST THREADS. 4) SURFACE ROUGHNESS 63 √ MIL-STD-10. 5) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 6) REMOVE ALL BURRS		SV Microwave, Inc. 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409		
FINISH: SEE NOTES								
SURFACE AREA: N/A		THIRD ANGLE PROJECTION 		DRAWN: JMC 04/16/04		TITLE: SMP R/A CABLE JACK FOR Ø.086 S.R. CABLE		
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.				CHECKED: STW 05/21/04				
				APPROVED: STW 05/21/04				
				E.M. SIMULATION: N/A		SIZE B	CAGE CODE 95077	DWG. NO. 1214-4001
				SCALE: 12:1		SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[1214-4001](#) [1211-66126](#) [SF1211-66074](#) [SF1211-66075](#) [SF1211-66076](#) [SF1211-66073](#) [SF1211-66077](#) [SF1211-66070](#) [SF1211-66069](#) [SF1211-6041](#) [1211-66164](#) [SF1211-6043](#)