




REV. 1 1/25/94

COIL: 0 +25 °C

RESISTANCE 700 OHMS ± 10%

NOMINAL VOLTAGE 20.0-30.0 VDC

MUST OPERATE 13.5 VDC

MUST RELEASE 8.0 VDC MAX, 1.5 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's


SHOCK 100 g's 11 MS DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE TIME 4 MS MAX

CONTACT BOUNCE 2 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2 AMPS
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 6/3/92 CK. 1/25/94

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. GENICOM
CUST. NO. 3SAVS002H1

TYPE 'HFW' RELAY

HFW1101K13