


LED

Digital RGB Flex Strip



Blueview
Electronics-optic
Technology Co., Ltd

Digital RGB Flex Strip

Part No.:BV-Flex-Dot-48-RGB

- ✧Cutttable each three LEDs
- ✧12VDC
- ✧Color change LED by LED



RoHS



Part NO.:

BV-Flex-Dot-48-RGB



Application:


- Outdoor illuminating letter
- Outdoor light box
- Outdoor advertising sign
- Outdoor architectural decoration
- Other lighting projects

Features:

- Dynamic color chasing, sequencing, changing and also static color modes available on Blueview's controller
- 12V DC input both indoor and outdoor available
- Maximum gray scale could be 256*256*256
- Standard length: 5m per reel
- Each three LEDs can be cut
- LED can be individually controlled






Structure Dimensions:



Notes: 1. All dimension units are millimeters.
2. All dimension tolerance is $\pm 1\text{mm}$ unless otherwise noted

Technical Parameter: (TA=25℃)

Part No.	Color	Operating Voltage(V)	Current (A)	Wattage (W)	Peak Wavelength (nm)	View Angle	Size	LED Qty
							(mm)	
BV-Flex-Dot-48-RGB	 Red	12	≤0.24		626			48
	 Green	12	≤0.24		525			
	 Blue	12	≤0.24		470			
	RGB		≤0.72	≤11.52		100°	1000*10	

Packing:



Quantity : 5m/roll
Size : 24×21.5 (cm)